



— PRODUCT DATA SHEET

Powerbank Flex7



— Powerbank Flex7

PRODUCT DESCRIPTION

Flexible, sustainable, powerful - this is what distinguishes our Powerbanks belonging to the Flex series. Offering six functions in a robust and water-resistant housing it provides: powerbank, battery charger with charge level indicator, secure battery storage, two separate displays for capacity check, double protection against short circuits, fast battery replacement. The Powerbank Flex7 contains two batteries type 18650 (included).

- Powerbank for charging mobile devices
- Green concept: less electronic waste as used batteries can be replaced
- Suitable for outdoor activities due to water and dust protection IP65 / special USB ports
- Charger with up to 30% shorter charging time (compared to charging in e.g. a flashlight P7R)
- Included batteries can be used directly in the suitable products, thus no loss of capacity or time

USABLE WITH

F1R, H8R, MH10, MH11, ML6, ML6 Connect WL, ML6 Warm Light, MT10, NEO10R, P6R Core, P6R Signature, P6R Work, P7R, PL6, iA6R, iH11R, iH8R

TECHNICAL DATA

Length [mm]	109
Width [mm]	47
Height [mm]	27
Weight [g]	164
Weight without batteries [g]	116
Material	PC

POWER SUPPLY

Power source type	Rechargeable battery
Battery quantity	2
Battery type	Li-ion
Battery description	18650 3.6V
Total battery voltage [V]	3.6
Total battery capacity [mAh]	6800
Total battery energy ² [Wh]	24.68
Rechargeable	Yes
Charging time ⁵ [min]	240
Charging technology	Internal
Energy status indicator	Battery Indicator, Charge Indicator, Low Battery Warning

PACKAGING INFORMATION

Type of packaging	Window Box
Scope of delivery	1 set of rechargeable batteries, USB cable
Item No.	502125
Customs tariff number	85076000900
MSRP price (€)	54.90

SINGLE PACKAGE

Dimensions W x H x D [cm]	8.4 x 14.3 x 3.3
Gross weight [g]	244
GTIN-13	4058205019224

EXPORT CARTON

Unit	48
Dimensions W x D x H [cm]	31.5 x 23.5 x 39
Gross weight [kg]	12.232
GTIN-13	4058205019248

FOOTNOTES

The information pertaining to scope of delivery, appearance, performance, dimensions and weight corresponds to the information available at the time of publication. In the interest of product development, we reserve the right to change scope of delivery, appearance, design and color without prior notice. Product images may vary from the actual products and may show optional accessories which can be purchased separately. Errors and omissions excepted.

2) Calculated capacity value in watt-hours (Wh). This applies to the delivery state of the battery/ies inside the respective item, or for lights with rechargeable battery/ies, to the rechargeable battery/ies inside the product when fully charged.

5) Charging time varies by hardware used.