

MINI VACUUM CLEANER (and accessories)

41-098-5011_5012

Special field service and EPA portable mini vacuum cleaner, to remove dust and debris from electronic equipment which is highly sensitive to contamination and static build up.

Features

- 'Blowvac' cleaner – full suction and blow off power control
- Durable yet compact construction
- Fully EPA compliant to IEC 61340-5-1
- Quality electronic component for reliability
- Conductive accessories including hard and soft nozzles and carrying strap
- Special 1.2 litre multi-layer filter system
- Low noise yet retaining excellent suction strength



Product Specifications

Voltage:	230V (Europe)
Motor:	880W (Electrical consumption)
Material:	Volume dissipative PP
Suction power:	160 mbar
Airflow:	Max. 35 L/sec
Sound Level:	Approx. 72 dB
Weight (appliance):	Approx. 2.2 kgs
Measurements:	31,5 x 12 x 18,5 cm (LxWxH)
Surface resistance:	10 ⁷ -10 ⁸ Ω
Diameter accessories:	32 mm
Cordset length:	3 Meters
Capacity:	Approx. 1 Ltr


Part Number and Description of the mini vacuum cleaner

41-098-5011	Vacuum sealer
41-098-5012	Vacuum sealer with electronic potentiometer

Part Numbers and Description of the Accessories

Cleaning related attachments (except blow assemblies) suit vacuum & blow use !

41-098-6021 41-098-6001



ESD-SAFE ACCESSORIES EPA BLOWVAC 555-ESD-S (HEPA) / 555-ESD-S-E (HEPA)



Cleaning related attachments (except blow assemblies) suit vacuum & blow use !



PH-707 ESD




PH-710 BKC ESD




PHU-05 ESD



PHU-16 ESD



PH-724



PH-708 ESD




PH-711 BKC ESD



PHU-07 ESD



PHU-18 ESD



PH-725



PH-708L ESD



PH-712 BKC ESD



PHU-08 ESD



PHU-19 ESD



PH-726



PH-709



PH-710




PHU-09 ESD



PHU-20 ESD



PH-705 ESD



PH-710 ESD




PH-710



PHU-10



PHU-22 ESD



PH-706 ESD



PH-711 ESD



PHU-04 ESD



PHU-11 ESD
PHU-12 ESD
PHU-13 ESD



PHU-26 ESD

WARNING ! "ESD" ATTACHMENTS ARE DESIGNED TO FUNCTION IN ESD-SAFE MODE IN EPA ENVIRONMENTS OR WITH EPA BLOWVAC'S CONNECTED TO A PROPERLY EARTHED POWER OUTLET ONLY !

41-098-6022 SOFT BRUSH
41-098-6009 MEDIUM BRUSH
41-098-6008 MED/HARD BRUSH