

## FEATURES

- Spring steel  
Easy fasten in application with a screw or bolt.
- Reusable so could be repositioned.
- Widely used across many industries or commercial and domestic situations
- Widely recyclable
- Rilsan is extremely hard waring
- Different colour options, Black or White to stand out or blend in.
- Multiple uses from engineering to DIY
- 

## RS PRO Spring Clips

See Stock Numbers listed below



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Family Name

### Product Description


Wide Base Tool Clips are manufactured from High Carbon Spring Steel strip and are finished with a black or white Rilsan coating.

The spring clips fasteners allow the cylindrical objects to be quickly snapped into place or pulled out through spring tension

The strength of the grip varies according to the material used & the thickness of the gripping arms, but all provide a sturdy connection that will withstand gravity, pressure & vibration

All clips usually have one fixing hole, however size 50.8mm has two fixings.

### General Specifications



RS part No	Size		H * +0.254mm/-0mm +0.0010"/-0"		W		T		C		E	
	Inch	mm	Inch	mm	Inch	mm	Inch	mm	Inch	mm	Inch	mm
289540 507832	1/4	6.35	.092	2.34	1/4	6.35	.0148	.376	17/32	13.49	19/32	15.08
289556 507826	3/8	9.53	.092	2.34	1/4	6.35	.0164	.419	5/8	15.88	25/32	19.84
289562 507810	1/2	12.7	.115	2.92	5/16	7.94	.018	.457	53/64	21.03	31/32	24.61
289578 507804	5/8	15.88	.115	2.92	5/16	7.94	.022	.558	31/32	24.61	1.5/32	29.37
289584 507797	3/4	19.05	.147	3.73	5/16	7.94	.024	.610	1.1/8	28.58	1.3/8	34.93
289590 507781	1	25.4	.147	3.73	5/16	7.94	.022	.558	1.3/16	30.16	1.5/8	41.28
289607 507775	1.1/8	28.58	.147	3.73	3/8	9.53	.028	.711	1.9/16	39.69	1.15/16	49.21
289613 507769	1.1/4	31.75	.147	3.73	7/16	11.11	.032	.813	1.45/64	43.26	2.1/8	53.98



## Family Name

289629 507753	1.1/2	38.1	.147	3.73	1/2	12.7	.036	.910	2	50.8	2.1/2	63.5
------------------	-------	------	------	------	-----	------	------	------	---	------	-------	------

Part numbers 2\*\*\*\*\* = White finish

Part numbers 5\*\*\*\*\* = Black finish

\*H: Hole diameter – above dimensions are in the off-press condition, coating can reduce hole diameters.

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories