

Cellular antenna 2G/3G/4G + NB IoT

SmartDisc is a low profile antenna with durable design. The antenna is ground plane independent enabling flexible and easy installation. Ideal for M2M applications and vehicle installations.

- 790-960MHz, 1710-2690MHz and NB IoT
- Discreet design with hole or adhesive mount
- IP67 class
- DC short
- Designed in Sweden with Patented technology

Specifications

Electrical					
Frequencies	790-960MHz				
	1710-2690MHz				
Impedance	50Ω				
Polarization	Vertical				
VSWR	3:1				
Gain	790-960MHz	2.15dBi			
	1710-2690MHz	3.15dBi			
Max power	10W				
Mechanical					
Dimensions (D x H)	96 x 26mm				
Installation	Hole mount with center screw				
	Std screw: Mate	erial thickness ≤ 3.5mm			
	Long screw: Ma	terial thickness ≤ 23.5mm			
	Hole dimension Ø 19mm				
	Min. installation radius 1000mm				
	Adhesive mount				
	Installation type is defined by part number acc. to below.				
Cable	RG316, brown				
	Cable length is defined by part number acc. to below.				
Connector	Connector type is defined by part number acc. to below.				
Weight	~190g				
Material	PC/PBT/Aluminum alloy				
Color	Black or White				
	Color is defined by part number acc. to below.				
IP class	IP67	IP67			
Temperature	Storage	-40°C to +85°C			
	Operating	-40°C to +85°C			









Other

This part is RoHS compliant.



Hole mount



Adhesive mount

Part number	Color	Installation type	Cable length (m)	Connector type
710213	Black	Std screw	0,5	SMA(m)
710214	White	Std screw	0,5	SMA(m)
710215	Black	Adhesive tape	0,5	SMA(m)
710218	White	Adhesive tape	0,5	SMA(m)
710211 / 707201	Black	Std screw	2,5	SMA(m)
710212	White	Std screw	2,5	SMA(m)
710221	Black	Adhesive tape	2,5	SMA(m)
710219	White	Adhesive tape	2,5	SMA(m)
710237	Black	Std screw	5,0	SMA(m)
710216	Black	Std screw	2,5	FME(f)
710232	Black	Long screw	2,5	SMA(m)
710279	White	Std screw	0,5	N-type (f)
710425	White	Long screw	2,5	SMA (m)
710201	Black	Std screw	1,0	Fakra (f)

Other cable lengths and connectors are available upon request.

Accessories

707154	White angled bracket
201411	Vertical bracket

Smarteq reserves the right to change specifications without prior notice.



Vertical bracket



Angled bracket





