

FEATURES

- Body material is AISI 304 stainless steel sheets
- IP66 rating
- Double lipped edges to ensure higher strength and ease of installation
- Easy to use, including removal of the door
- Door is fitted with a polyurethane gasket

RS PRO Wall Boxes - 304 Stainless Steel Wall Box [RS / V2 / AISI 304]

RS Stock No.: 7586968



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Wall Boxes



Product Description

RS Pro IP66 Wall Boxes

Brought to you by RS Pro, a range of stainless steel wall mounted enclosures. Rated at IP66, the level of protection provided by these boxes ensures the contents will be safely stored and protected. The door of the enclosure has a pull out hinge which allows it to be removed for easy access and due to the protection benefit, these wall boxes are suitable for various applications. All models are highly reliable and excellent quality.

General Specifications

| Body Material | 304 Stainless Steel | | | | |
|------------------------|--------------------------------|--|--|--|--|
| Number Of Doors | 1 | | | | |
| Colour | Unpainted | | | | |
| Gland Plate | No | | | | |
| Door Lock Type | Quick Release Lock | | | | |
| Chassis Plate | Yes | | | | |
| Transparent Door | No | | | | |
| Fixing Kit | No | | | | |
| Application | Electrical | | | | |
| External Mounting Type | Bracket | | | | |
| Internal Mounting Type | Panel | | | | |
| Special Features | 120° Door Opening | | | | |
| For Protection Of | Sensitive electrical equipment | | | | |

Mechanical Specifications

| External Height | 600 mm |
|-----------------|--------------------------------|
| External Depth | 250 mm |
| External Width | 600 mm |
| Dimensions | H.600 mm x W.600 mm x D.250 mm |

Protection Category

| ID Deting | IDOG |
|-----------|------|
| IP Rating | IP66 |



Approvals

| Declarations | RoHS Certificate of Compliance |
|--------------|--------------------------------|
|--------------|--------------------------------|

Similar Products

| Stock No. | Brand | Product Name | Colour | Body Material | Dimensions |
|-----------|--------|---------------------------------------|-----------|------------------------|--------------------------------|
| 758-7065 | RS PRO | 304 Stainless Steel Wall Box | Unpainted | 304 Stainless Steel | 200 mm x 300 mm x 120 mm |
| 758-6964 | RS PRO | 304 Stainless Steel Wall Box | Unpainted | 304 Stainless Steel | 600 mm x 400 mm x 200 mm |

Additional Information / Installation Diagrams / Illustrations / Accessories

