

## FEATURES

- Steel structure, coated with an epoxy polyester powder
- IP66 rating
- Enclosure and the door is made from sheet steel
- Fully wall mountable
- Pebble grey finish

# RS PRO Wall Boxes- Steel Wall Box

RS Stock No.: 775-5794



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

### RS Pro IP66 Sheet Steel Wall Boxes

From RS Pro, a range of incredibly useful steel wall mounted enclosures. Enclosures are present in almost every industry and can store all manor of items, such as medical equipment or electronics. These boxes are rated at IP66 and provide an excellent degree of protection, whether it's used within an indoor or outdoor environment. With various sizes available, they are suitable for a wide selection of applications. All models are highly reliable and excellent quality.

## General Specifications

<b>Body Material</b>	<b>Steel</b>
<b>Number Of Doors</b>	<b>1</b>
<b>Colour</b>	<b>Grey</b>
<b>RAL Code</b>	<b>RAL7032</b>
<b>Gland Plate</b>	<b>Yes</b>
<b>Door Lock Type</b>	<b>Single Lock System</b>
<b>Chassis Plate</b>	<b>Yes</b>
<b>Transparent Door</b>	<b>No</b>
<b>Fixing Kit</b>	<b>Yes</b>
<b>Application</b>	<b>Electrical, Electronic, Industrial</b>
<b>External Mounting Type</b>	<b>Bracket</b>
<b>Internal Mounting Type</b>	<b>Panel</b>
<b>Special Features</b>	<b>IK10 Against Mechanical Impacts</b>
<b>For Protection Of</b>	<b>Sensitive electrical equipment</b>

## Mechanical Specifications

<b>External Height</b>	<b>300 mm</b>
<b>External Depth</b>	<b>200 mm</b>
<b>External Width</b>	<b>400 mm</b>
<b>Dimensions</b>	<b>H 300 mm x D 200 mm x W 400 mm</b>
<b>Thickness</b>	<b>Enclosure &amp; door 1.2mm or 1.5mm sheet steel</b>

**Protection Category**

IP Rating	IP66
-----------	------

**Approvals**

Declarations	RoHS Certificate of Compliance
--------------	--------------------------------

**Similar Products**

Stock No.	Brand	Product Name	Colour	Body Material	Dimensions
189-6587	RS PRO	Steel Wall Box	Grey	Steel	250 mm x 200 mm x 150 mm
775-5381	RS PRO	Steel Wall Box	Grey	Steel	1200 mm x 800 mm x 300 mm

Additional Information / Installation Diagrams / Illustrations / Accessories

