

Plug and play on-the-go.

DELL EXTERNAL USB SLIM DVD +/- RW OPTICAL DRIVE - DW316



At home or on-the-go

The Dell External USB Slim DVD +/- RW Optical Drive is a plug and play disc burning and disc playing solution that you can use at home or on the go.

Simply plug the low profile (14mm), lightweight (200g) drive into your Ultrabook or notebook's USB port and you'll be ready to play or burn your favorite DVD or CD at home in even a small workspace. Or, place the drive in your bag to take this functionality with you.

Easy to use

Take advantage of the bundled CyberLink Media Suite to easily play and burn DVD/CDs, or install disc-based computer programs.

This premium, external optical drive is powered by your Ultrabook's or notebook's USB port, so no batteries or power cords are necessary.

Versatile, sleek and portable design

The Dell External USB Slim DVD +/- RW Optical Drive has a streamlined design, which compliments contemporary notebooks and blends in well with your home workspace or a high tech café.

Enjoy peace of mind

Purchase with confidence and rely on the protection of a 1-Year Limited Hardware Warranty for your Dell External USB Slim DVD +/- RW Optical Drive.



Easily portable

Slim, lightweight without the need for a battery or power cords necessary.



Plug-and-play

Plug in the drive and play or burn DVDs and CDs.



Peace of mind

Rely on the protection of a 1–Year Limited Hardware Warranty.

Features & Technical Specifications



Feature	Technical Specification	Feature	Technical Specification
Product Type	External DVD ±RW drive	OS Required	Microsoft Windows 7 / 8 / 8.1 / 10
Interface	USB 2.0	Features Dimensions	Manual Emergency Disc Eject Hole, Active Optimum Power Control (AOPC), CPRM support
Read Speed	24x (CD) / 8x (DVD)		
Write Speed	24x (CD) / 8x (DVD±R) / 6x (DVD±R DL)		Depth: 5.4in / 137.5mm Width: 5.7in / 144mm Height: 0.6in / 14mm
Media Load Type	Tray		
Optical Storage	DVD±RW (±R DL) / DVD-RAM		
Buffer Underrun Protection	Automatic Buffer Under Run Error Protection Technology	Weight (ounces / pounds) Warranty In the box	7.05 oz / 200 g
	<i>5,</i>		1 year Limited Hardware Warranty
Buffer Size	0.75 MB		Dell External USB Slim DVD +/- RW Optical Drive 1 x USB cable - external - 2 ft CyberLink Media Suite CD
Supported Media Formats	CD Extra, CD-DA (audio), CD-I, CD-ROM XA, Photo CD, Video CD, CD-ROM, DVD-Video, DVD-Audio, Super Video CD, Super Audio CD Hybrid Disc		
Supported Media Types	CD-ROM, CD-R, CD-RW, DVD-ROM, DVD-R, DVD-RAM, DVD-RW, DVD+RW, DVD+R,		

DVD+R DL, DVD-R DL, M-DISC