One-handed rapid slide focus mechanism - spot (x1) to flood (x7)

Beam intensifying plano-convex optical lens

Robust high grade aluminium lamp body Adjustable head lamp swivels through 90°

Detachable head lamp & battery pack

Water & dirt resistant, tested to IP64

Battery life: high - 5hrs, dimmed - 12hrs

**200 LUMENS** 200

## Item No: T9620

SPOT : FLOOD	MAX Range	WEATHER Rating	IMPACT RESISTANT	POWER Supply	BATTERY Life
X1: X7	250M	IP64	1M	4 x AA (not included)	UP TO 12 HOURS



## Item No: T9610

SPOT : FLOOD	MAX	WEATHER	IMPACT	POWER	BATTERY
	Range	Rating	RESISTANT	Supply	Life
X1: X7	200M	IP64	1M	3 x AAA (not included)	UP TO 13 HOURS

# CK LED HEAD TORCH 120 LUMENS

**COMPACT AND LIGHTWEIGHT, THE C.K T9610** IS A REMARKABLY POWERFUL HEAD TORCH **FOR ITS SIZE.** 

High Power 120 Lumen Cree XR-E Q3 LED

3 lighting modes: high, dimmed, flash

One-handed rapid slide focus mechanism - spot (x1) to flood (x7)

Beam intensifying plano-convex optical lens

Robust high grade aluminium lamp body

Adjustable head lamp swivels through 90°

Water & dirt resistant, tested to IP64


Battery life: high - 5hrs, dimmed - 13hrs

# **C.K HAND TORCHES**

## K LED HAND TORCH 150 LUMEN

**AN IMMENSELY VERSATILE HIGH** PERFORMANCE HAND TORCH, THE C.K T9520 **HAS AN IMPRESSIVE 250M RANGE SPOT BEAM AND AN EXTENSIVE X30 FLOOD BEAM.** 

# 150 LUMENS **150**



High Power 150 Lumen Cree XR-E Q5 LED

3 Lighting modes: high, dimmed, flash

One-handed rapid slide focus mechanism

- spot (x1) to flood (x30)

Beam intensifying plano-convex optical lens

Robust high grade aluminium body

Water & dirt resistant, tested to IP64 Battery life: high - 5hrs, dimmed - 14hrs

Size: 133 x 40mm



## Item No: T9520

SPOT : FLOOD	MAX Range	WEATHER Rating	IMPACT RESISTANT	POWER Supply	BATTERY Life
X1: X30	250M	IP64	1M	3 x AAA (not included)	UP TO 14 HOURS

# **120 LUMENS**

## Item No: T9510

SPOT : FLOOD	MAX	WEATHER	IMPACT	POWER	BATTERY
	Range	Rating	RESISTANT	Supply	Life
X1:X10	150M	IP64	1M	3 x AAA (not included)	UP TO 16 HOURS

## C.K LED HAND TORCH 120 LUMENS

8

POWER

**COMPACT YET POWERFUL, THE C.K T9510** ALSO HAS A DIMMED BEAM MODE FOR **GLARE-FREE CLOSE PROXIMITY USE.** 

## PECIFICATION

High Power 120 Lumen Cree XR-E Q5 LED

3 Lighting modes: high, dimmed, flash

One-handed rapid slide focus mechanism - spot (x1) to flood (x10)

Beam intensifying plano-convex optical lens

Robust high grade aluminium body

Water & dirt resistant, tested to IP64

Battery life: high - 6hrs, dimmed - 16hrs

Size: 107 x 30mm



