

COMFORT SPILL MAT - THE ABSORBING ANTI-FATIGUE MAT!

The Comfort Spill Mats from SPC are a combination of an absorbent matting fitting inside an anti-fatigue mat.

- Design provides buoyancy for basic fatigue relief.
- Silicone free allowing it to be used in vehicle painting facilities.
- High quality nitrile rubber makes the mat oil resistant.
- Rough surface allows sorbent to “grip” anti-fatigue mat.
- Allows you to keep workers safe while protecting the floor from oils and other industrial liquids.
- Available in an “Oil Only” version as well as a “Maintenance” version for use with general industrial liquids.



Kits				
Order Reference	Article No.	Description	Total Qty/Pack	Absorption Capacity (Ltrs)
SA-AFO	813829	OIL ONLY KIT - incl. 1 perforated roll of 76 cm x 46 m & 1 anti-fatigue base mat of 82 cm x 152 cm	1 Kit	187
SA-AFA	813830	MAINTENANCE KIT - incl. 1 perforated roll of 76 cm x 46 m & 1 anti-fatigue base mat of 82 cm x 152 cm	1 Kit	187

Refills				
Order Reference	Article No.	Description	Total Qty/Pack	Absorption Capacity (Ltrs)
OP30-P-E	813755	ROLL, 76 cm x 46 m, Heavy weight, perforated & bonded	1 Roll(s) / Box	187
MRO30-P-E	813823	ROLL, 76 cm x 46 m, Heavy weight, perforated & bonded	1 Roll(s) / Box	185

BATTEMAT - CAMOUFLAGE PATTERNED ROLLS. TOUGH COVER LAYER HIDES LEAKS AND DRIPS FOR LONGER USE, OFFERS SURE FOOTING AND IS IDEAL FOR AREAS WITH MODERATE FOOT TRAFFIC.

- Absorbs spills & leaks of any liquid: oils, coolants, water and solvents.
- Camouflage pattern hides dirt and reduces premature replacement.
- Durable abrasion resistant top layer stands up to moderate foot traffic.
- Ideal for use in walkways, production & machine areas, under assembly lines, etc.
- Perforations available for flexibility: easy to tear off the desired length, minimises waste.



Order Reference	Article No.	Description	Total Qty/Pack	Absorption Capacity (Ltrs)
BM15-E	813833	ROLL, 38 cm x 46 m, Heavy weight, double perforated & bonded	1 Roll(s) / Dispenser box	99
BM30-E	813834	ROLL, 76 cm x 46 m, Heavy weight, double perforated & bonded	1 Roll(s) / Box	197
BM30X-E	813835	ROLL, 76 cm x 46 m, Heavy weight, bonded	1 Roll(s) / Box	197

BSM - NON-SLIP & IMPERMEABLE MATS. PERFECT FOR HIGH TRAFFIC AREAS AND WALKWAYS THAT NEED TO BE DRY, CLEAN AND SLIP-FREE.

- Non-slip, impermeable barrier film sticks the mat to the floor and prevents liquids from leaking through. For best results, clean the floor before use.
- Backing resists curling and buckling.
- Needle-punched polypropylene fibres make product tear resistant, ideal for use in high traffic areas.
- Absorbs oil, water and non-aggressive chemicals.
- Prevents unsightly tracking between areas.



Order Reference	Article No.	Description	Total Qty/Pack	Absorption Capacity (Ltrs)
BSM3650	813838	MAT, 91 cm x 15.25 m, Medium weight, barrier backing	1 Roll(s) / Bag	46
BSM100	813839	MAT, 91 cm x 30.48 m, Medium weight, barrier backing	1 Roll(s) / Bag	95

BSM creates a dry and slip free workplace.