

FEATURES

- Both 290 mm and 550 mm height versions available
- 30 drawer versions suiting all your requirements
- Grey polypropylene (PP) cabinet
- Drawers manufactured from crystal clear polystyrene (PS)
- Galvanised steel shelves
- Temperature tolerance (-40 to +55°C)
- Self-adhesive labels supplied for each drawer
- Flexible and efficient storage

RS PRO 30 Drawer Storage Unit, PP, 290mm x 310mm x 180mm, Grey

RS Stock No.: 909-6934



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From RS PRO these plastic storage cabinets are ideal for all your everyday storage needs. They are built from a hard-wearing plastic, with galvanised steel shelves, making these units both durable and long lasting. They are ideal for storing all your small parts, as well as providing easy access

General Specifications

Drawers	30
Drawer Material	PP
Case Material	PP
Colour	Grey
Cabinet / Trolley Capacity	240kg; 144kg
Capacity Per Shelf	50kg (UDL)
Number Of Dividers Supplied	30
Number Of Divider Locations Per Drawers	7; 3; 5
Drawer Type	L-00; L-07
Transparent Drawers	Yes
Tilt Drawers	Yes
Wall Mounted	No
Applications	Garages, Workshops, Warehouses, Factories

Mechanical Specifications

Overall Height	290mm
Overall Width	310mm
Overall Depth	180mm
Weight	4.6kg

Storage Drawer Dimensions

Storage Drawer Size (H x W x D)	Quantity Of Storage Drawer	Each Drawer Capacity
37mm x 55mm x 175mm	5 x 6	5kg

Operation Environment Specifications

Temperature Tolerance	-40°C to 55°C
-----------------------	---------------





Cabinet Size HxWxD(mm)	Drawer Type	No of Drawers in Cabinet	Each Drawer External Size HxWxD(mm)	Each Drawer Internal Size HxWxD(mm)	RS Stock No
290mm HIGH CABINETS					
290 x 310 x 180	L-00	30	37 x 55 x 175	32 x 47 x 146	9096934
290 x 310 x 180	L-01	24	37 x 69 x 175	32 x 61 x 146	9096943
290 x 310 x 180	L-02	12	37 x 138 x 175	32 x 128 x 146	9096946
290 x 310 x 180	L-04	12	59 x 92 x 175	55 x 82 x 146	9096940
290 x 310 x 180	L-06	4	59 x 277 x 175	55 x 266 x 146	9096959
290 x 310 x 180	L-07	6	81 x 138 x 175	74 x 128 x 146	9096952
550mm HIGH CABINETS					
550 x 310 x 180	L-00	60	37 x 55 x 175	32 x 47 x 146	9096956
550 x 310 x 180	L-01	48	37 x 69 x 175	32 x 61 x 146	9096965
550 x 310 x 180	L-02	24	37 x 138 x 175	32 x 128 x 146	9096968
550 x 310 x 180	L-04	24	59 x 92 x 175	55 x 82 x 146	9096962
550 x 310 x 180	L-06	8	59 x 277 x 175	55 x 266 x 146	9096971
550 x 310 x 180	L-07	12	81 x 138 x 175	74 x 128 x 146	9096974