

ENGLISH

Wi-Fi Digital Microscope

Code: 913-2478



This product is a very innovative handheld color digital microscope with Wi-Fi wireless transmission. It breaks the conception of traditional microscope to realize the following functions: measurement, conservation, copy and transfer of images and video which are difficult for a traditional microscope. It is a small, easy to operate light and portable fun. It can be used with all the most popular smartphones, tablet and even with PC.

Main applications:

- •Industrial Inspection •Electronics/mechanical assembly and quality control •Scientific teaching tool •School Research tool •Printing Inspection •Textile inspection
- Medical analysis Dermatology(skin/scalp)exam
- Hair and trichology inspection Insect dissection/observing
- Plant dissection/observing •Collections/jewelry Inspection
- Reading aid •etc.



Information

Operation system Windows ,OS X, iOS , Android (It can be used by Wi-Fi or USB)

Photo and Video Resolution 1.3MPixels-- 1280x1024(MJPG),640x480(MJPG), 320x240

Frame Rate <u>15fps@1280x1024,30fps@640x480</u> 320x240

Wi-Fi Protocol IEEE 802.11 b/g/n standards compliant

Wi-Fi Wireless Transmission Distance up to 5m

Transmit Power 11n HT40 MCS7: +13 dBm , 11b CCK: +18 dBm , 11g OFDM: +15

dBm

Data Rate 802.11n: up to 150Mbps , 802.11b: 1, 2, 5,5, 11Mbps , 802.11g: 6,

9, 12, 18, 24, 36, 48, 54Mbps

Frequency Range 2.400 ~ 2.4835GHz

Power Consumption Max 2.5W Frame Rate 10fps~30fps

Li-ion Battery

Continuous Working Time—Appx.2 Hours, Full Charging Time—

Appx.2 Hours

Power Source DC5.0V/1A

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.



ENGLISH

CAMERA Information

CMOS 1/4" Camera Sensor

Optical features Exposure: Auto, Gamma: Auto, White Balance: Auto, Black Reference: Auto,

MICROSCOPE Information

Magnification 5x~200x **Object Distance** 8~200mm

8mm ~ 200mm Focus Range

n. 8 adjustable White Led **Light Source**

Lens High Definition Microscopy Lens **Dimensions** 36mm(Diameter) x 142mm(Length)

Weight 88g

USB Information

Photo and Video

1.30Mpixel-1280x1024,640x480,320x240 Resolution

Frame Rate 15fps(1280x1024),30fps(640x480) 320x240

PC interface USB 2.0

MiniUSB Cable for


1.2m recharging

HOW TO INSTALL APPS (Example)

For *iPad* and *iPhone*: search "Mic-Fi" in App Store to download an install the app.

For Android's Smart-Phone and Tablet: search "Mic-Fi" in Google Play to download an install the app







OS X Nuivew Plus Plus

ENGLISH



Magnification, Working distance, field of view:

High Cover : 60x e 200x

Magnification	Worging distance	Field of view (x)	Field of view (y)	
10	157	39	29	
20	73	20	15	
30	41	13	10	
40	30	10	7.5	
50	22	8	6	
60	17	7	5	
80	14	5	4	
100	11	4	3	
150	13	2.5	2	
200	19	2	1.5	
Listed values may differ slightly				
Working distance				
Contact point:				Unit: mm
Low Cover: 80x e 150x				



ENGLISH

Raccommended Products					
913-2503	913-2500	913-2516			
Dimensions: (W)8cm x (L)15cm x	Dimensions: (W)12.7cm x	Dimensions: (W)12.7cm x			
(H)25cm	(L)20.7cm x (H)30.5cm	(L)20.7cm x (H)30.5cm			
The 913-2503 articulated desktop	The 913-2500 is a rigid vertical	The 913-2516 stand is designed			
stand holds the Mic-Fi microscope with a flexible gooseneck arm that	desktop stand that was designed to be used with the Mic-Fi digital	for use with the complete line of Mic-Fi digital microscope.			
can be bent and twisted into many	microscope. It provides about 20cm	This stand utilizes an adjustable			
positions.	of vertical working distance from the	sliding horizontal boom arm with			
This convenient and versatile stand	object.	up to 25cm reach and 360 degree			
is compatible with all Mic-Fi	-	rotational capability making it			
handheld microscopes, which allow		ideal for inspection applications			
the user with hands free stable		where the ability to extend out			
operations of the scope.		over and across a specimen is			
		required.			

Package:

- Wi-Fi Digital Microscope
- Trasparent Cap
- USB AC adapter
- USB cable
- Quick manual
- Plastic Stand
- Line Calibration Ruler