



Spray Dusters

All are manufactured from a non-flammable blend of gas and give off zero residue. There are a variety of strength on offer: standard, high power and super power as well as non-invertible and invertible aerosols to allow access to the most difficult of areas. All are supplied with a actuator so allow the strength of blast to be controlled.

Ideal for computers, keyboards, printers, timing devices, cash machines, fax machines, photocopiers, audio/video equipment, photo equipment, VCRs, CDs and delicate lab equipment.



Standard

Sprayduster

342ml / 400g. Standard power spray duster which must be used upright.

Ref: SDU400D

Sprayduster

87ml / 100g. The smallest of the range, extremely handy for mobile workers.

Ref: XSDU100

Sprayduster *(Eastern European)*

342ml / 400g. Non-invertible, must be used upright. Packaging contains English with Czech, Polish, Hungarian and Russian languages.

Ref: SDU400E

High Power

Souffl'sec

350ml / 400g. Non-invertible, must be used upright.

Ref: SFC400D



Super-Power

Super Duster

300ml / 350g. This compressed gas duster has the greatest of blast. One quick blast and your surfaces are instantly clean of all contaminants.

Ref: SPD300



Invertible

Standard strength spray dusters which can be inverted and sprayed in any direction without threat of dispensing any liquid on valuable equipment. Ideal for removing dust, lint and other contaminants from hard to reach places.



Sprayduster

125ml / 144g. Ref: SDU125D

Sprayduster

200ml / 231g. Ref: SDU200D

Super Duster Invertible

200ml / 231g. Can be used at any angle and still provides a powerful blast.

Ref: SPD1200D

*** CLEANING TIP** Keyboards boast anything up to 3500 microbes and the humble mouse 1500 microbes, clean yours today...

Product Finder

Spray Dusters	Unit Size	Qty Per Case	Power	Product Code	Application
Sprayduster	342ml / 400g	12	S	SDU400D	Ideal for use on keyboards, printers, fax machines, photocopiers and computers. Invertible versions are excellent for hard to reach places.
Sprayduster (Eastern European)	342ml / 400g	12	S	SDU400E	
Sprayduster	87ml / 100g	24	S	SDU100	
Sprayduster	125ml / 144g	12	S	SDU125D	
Sprayduster	200ml / 231g	12	S	SDU200D	
Souffl'sec	350ml / 400g	12	H	SFC400	
Super Duster	300ml / 350g	12	SU	SPD300	
Super Duster Invertible	200ml / 231g	12	SU	SPDI200D	

S – Standard H – High Power SU – Super Power

Wipes and Buds

AF supply a range of natural and synthetic wipes and buds for cleaning and drying a wide variety of surfaces. For use in conjunction with AF screen and surface cleaners to ensure a perfect result even in the most inaccessible areas.

Paper Wipes

High quality, lint-free single ply paper, safe to use on all screens and filters. Excellent strength wet or dry. Easy to recycle.

Computiss

50 sheets a pack. Ref: CTI050

Safetiss

200 sheets in a box. Ref: STI200



Synthetic Wipes

Tonerclene

25 Toner absorbent cloths, does not re-deposit toner, non-smearing and in a re-sealable bag.

Ref: TOC025

Safecloths

Non-woven 320 x 340mm cloths for general cleaning applications, such as equipment casings, furniture and whiteboards. For use with AF screen and surface cleaning products.

Ref: SCH050 (50 Cloths) / SCH025 (25 Cloths)



Cotton Wipes


100% pure cotton wipes with no additives or brightening agents. Re-useable and non-linting, friendly to the environment.

Safewipes

100 large cloths – 230 x 230mm
Ref: SWI100

Safewipes

4 individual bags of 100 wipes, 100 x 100mm in size. Ref: SWI400





Buds

Foambuds

Plastic sticks with foam bud for cleaning read/write heads and tape drives. Extra long (15cm) handle allows maximum access to area to be cleaned while maintaining pressure. Cotton bud under the foam provides a solvent reservoir. For use with Isoclene, Headclene, AF Spray or Safeclene 2000. Contains 4 bags of 25 buds.

Ref: FBU100

IPA Foam Buds

Plastic handles with foam buds with a reservoir handle holding IPA alcohol which is 'snapped' to release the solvent onto the spatula foam tip. Safe on most plastics (test on sensitive plastics before use).

Ref: FBUIPA25



PC Buds

Plastic spatulas tipped with wide flexible foam head for cleaning keyboards and slots. 13cm in length with a 13mm wide head. Abrasion resistance foam ensures thorough cleaning of surfaces. Flexibility of head allows easy access. Use with Foamclene, Maxiclene, AF Spray or Isoclene. Contains 25 buds in a re-sealable bag.

Ref: PCB025

Safebuds






Rigid wooden sticks tipped with pure cotton buds. Ideal for cleaning awkward corners and difficult to reach parts of computer hardware. Contains 10 bags of 100 buds.

Ref: SBU000

All these wipes can be recycled after use and when dry, they are made from recycled pulp and a chemical free process. The plastic tubs can also be recycled.

Product Finder

Wipes and Buds		Unit Size	Qty Per Case	Product Code	Application
Computiss	50 Sheets	10	CTI050	Screens and filters, general cleaning applications.	
Safetiss	200 Sheets	10	STI200		
Safewipes	100 Wipes	10	SWI100	General cleaning applications.	
Safewipes	400 Wipes	10	SWI400		
Tonerclene	25 Wipes	10	TOC025	Printers and photocopiers.	
Safeclths	25 Cloths	10	SCH025	Equipment casings, furniture and whiteboards.	
	50 Cloths		SCH050		
Foambuds	Contains 4 bags of 25 Buds	10	FBU100	Read/write heads and tape drives.	
PC Buds	25 buds	10	PCB025	Keyboards, slots and hard to reach areas.	
Safebuds	Contains 10 bags of 100 Buds	10	SBU000	Awkward corners and difficult to reach parts of computer hardware.	

The Fragrance Collection		Unit Size	Qty Per Case	Product Code	Application
 PC-Clene	100 wipes	12	CSSR	PC hard drives and monitor casings, printers, copier and fax machines.	
 Phone-Clene	100 wipes	12	CSSA	Desk telephones, mobile phones and hand-sets.	
 Screen-Clene	100 wipes	12	CSSW	Computer screens and laptops including TFTs and LCDs. Mobile phone, PSP and MP3 player screens.	
 Headset-Clene	100 wipes	12	CSSP	Plastic parts of head-sets.	
 Hand-Clene	100 wipes	12	CSSH	Hands	
Dry-Wipes	100 wipes	12	CSSD	General purpose - all areas.	
Clene-Swipe Starter Kit	4 tubs / 2 brackets	1	CSSK	Computer screens and laptops, mobile phone, PSP, MP3 players, plastic casings, printers copiers and fax machines.	
Clene-Swipe Mixed Wipes	100 wipes	12	CSSM		
Clene-Swipe Brackets	2 Brackets	5	CSTB02		N/A

If you are looking for a micro-fibre cloth, go to the Retail Range section...

www.af-net.com



The Fragrance Collection

A range of pre-saturated wipes to keep your personal workspace clean, fresh and subtly fragrant. Clene-Swipes remain moist over long periods. Special antibacterial properties help kill germs that can cause coughs, colds, skin problems and worse. The anti-static properties reduce the build up of dust and dirt.



PC-Clene

With fruity *raspberry* fragrance. Contains anti-static properties for use on all plastic office equipment – PC hard drives and monitor casings, printers, copier and fax machines.

Ref: CSSR



Dry-Wipes

Multi-purpose dry wipes. Excellent wet strength for mopping up spills. Can be used as a general purpose cleaner as well as a soft tissue for personal care.

Ref: CSSD



Phone-Clene

With uplifting *aloe vera* fragrance. Contains anti-bacterial properties for use on telephones and mobile phones to clean and sanitise.

Ref: CSSA



Screen-Clene

With invigorating *white rapids* fragrance. Contains anti-static properties and is non-alcoholic for use on computer screens and laptops including TFTs and LCDs.

Ref: CSSW



Headset-Clene

With fresh *peppermint* fragrance. Contains anti-bacterial properties for use on plastic parts of headsets.

Ref: CSSP



Hand-Clene

Wash your hands without water. Effective hand hygiene anywhere and anytime. Gentle on the skin and removes ink and grime.

Ref: CSSH



Clene-Swipe Starter Kit

PC/Screen/Telephone/Headset cleaner. Complete starter kit. Specially designed to be easily accessible, the starter kit contains 2 wall brackets which hold 4 tubs.

Ref: CSSK

Clene-Swipe Mixed Wipes

PC/Screen/Telephone/Headset cleaner. A mixed set with 3 tubs of each – total 12 tubs.

Ref: CSS

The brackets come with strong adhesive pads and screws to make putting them up in a centralised handy place easy!

Clene-Swipe Brackets

A pack containing 2 brackets, each hold two tubs.

Ref: CSTB02M



www.af-net.com