

> With funnel nozzle



Kit 1 ALFA Funnel Nozzle



Order No.	Description
T0053657199	Easy-Click-60 extraction arm with funnel, width 230 mm, height 100 mm, flexible arm, Ø 60 mm, length 1 m, with stop valve
Consists of:	
T0053657499	Stop valve with bench mounting brackets
700-3051-ESD	Extraction hose, flexible, 3 m, Ø 60 mm
OF10	Extraction arm Ø 60 mm, 1 m
ALFA	Funnel nozzle

> With sloped nozzle



Kit 1 Sloped Nozzle



Order No.	Description
T0053657299	Easy-Click-60 extraction arm with sloped nozzle, Ø 60 mm, length 1 m, stop valve
Consists of:	
T0053657499	Stop valve with bench mounting brackets
700-3051-ESD	Extraction hose, flexible, 3 m, Ø 60 mm
OF10	Extraction arm Ø 60 mm, 1 m
FT-NL	Sloped nozzle

> Extraction arm for applications with limited space, such as under a microscope



Kit 1 32 Sloped Nozzle



Order No.	Description
T0058762770	Easy-Click-60 extraction arm with sloped nozzle Ø 32 mm, length 1 m, Ø 32 mm, stop valve
Consists of:	
T0053657499	Stop valve with bench mounting brackets
700-3051-ESD	Extraction hose, flexible, 3 m, Ø 60 mm
T0053658099	Extraction arm Ø 32 mm, 1 m
T0058762834	Sloped Nozzle

> 2 joint arm and sloped nozzle



Kit 1S Sloped Nozzle



Order No.	Description
T0053657999	Easy-Click-60 2 joint aluminium extraction arm with sloped nozzle, stop valve, length 1.5 m
Consists of:	
T0053659899	2 joint arms with stop valve and bench mounting brackets
700-3051-ESD	Extraction hose, flexible, 3 m, Ø 60 mm
OF07	Flex. extraction arm Ø 60 mm, 0.7 m
FT-NL	Sloped nozzle

> 1 joint arm and funnel nozzle



Kit 1S Funnel Nozzle



Order No.	Description
T0058762763	Easy-Click-60 1 joint aluminium extraction arm with funnel nozzle, stop valve, length 1.14 m
Consists of:	
T0058762747	1 joint arm with stop valve and bench mounting brackets
700-3051-ESD	Extraction hose, flexible, 3 m, Ø 60 mm
OF07	Flex. extraction arm Ø 60 mm, 0.7 m
ALFA	Funnel nozzle