

Alpha Wire | 711 Lidgerwood Avenue, Elizabeth, NJ 07207 Tel: 1-800-52 ALPHA (25742), Web: www.alphawire.com

Request a Sample

# Customer Specification PART NO. 67150

#### Construction

		Diameters (mm)
1) Component 1	1 X 1 HOOKUP	
a) Conductor	1.50 (84/0.16) mm <sup>2</sup> Tinned Copper	1.62
b) Insulation	0.280 mm Wall, Nom. Modified Polyphenylene Ether	2.18+/- 0.05
(1) Print	ALPHA WIRE-* P/N 67150 ECOWIRE TM 1.5MM2 E163869 RU AWM 11028 105C 600V VW-1 CRU AWM I A/B 105C 600V FT1 CE ROHS * = Factory Code	
(2) Color(s)	BLACK, RED, WHITE, BLUE, GREEN, BROWN ORANGE, VIOLET, GREEN/YELLOW	I, YELLOW

### Applicable Specifications

1) UL	AWM/STYLE 11028	105°C / 600 V <sub>RMS</sub>
	VW-1	
2) CSA International	C(RU) AWM I A/B FT1	105°C / 600 V <sub>RMS</sub>
3) Other	Halogen-Free	
	IEC 60332-2 Flame Behavior	
4) CE:	EU Low Voltage Directive 2014/35/EU	

#### Environmental

1) EU Directive 2011/65/EU(RoHS2):	
	All materials used in the manufacture of this part are in compliance with European Directive 2011/65/EU and the amending Directive 2015/863/EU of 4 June 2015 regarding the restriction of use of certain hazardous substances in electrical and electronic equipment. Consult Alpha Wire's web site for RoHS C of C.
2) REACH Regulation (EC 1907/2006):	
	This product does not contain Substances of Very High Concern (SVHC) listed on the European Union's REACH candidate list in excess of 0.1% mass of the item. For up-to-date information, please see Alpha's REACH SVHC Declaration.

## Properties

Physical & Mechanical Properties		
1) Temperature Range	-40 to 105°C	
2) Bend Radius	10X Cable Diameter	
Electrical Properties	(For Engineering purposes only)	
1) Voltage Rating	600 V <sub>RMS</sub>	
2) Inductance	0.11 μH/m, Nominal	
3) Conductor DCR	13.7 Ω/Km @20°C, Nominal	

## <u>Other</u>

Packaging	Flange x Traverse x Barrel (inches)	
a) 500 M	12 x 4.5 x 3.5 Continuous length	
b) 100 M	6.5 x 2 x 1.9 Continuous length	
c) 50 M	3.5 x 3 x 1.125 Continuous length	
	[Spool dimensions may vary slightly]	
Notes:		

a) Certain colors and put-up combinations may only be available by special order, minimums may apply.

#### www.alphawire.com

Alpha Wire | 711 Lidgerwood Avenue, Elizabeth, NJ 07207 Tel: 1-800-52 ALPHA (25742)

Although Alpha Wire ("Alpha") makes every reasonable effort to ensure their accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha had been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

#### ALPHA WIRE - CONFIDENTIAL AND PROPRIETARY

Notice to persons receiving this document and/or technical information. This document is confidential and is the exclusive property of ALPHA WIRE, and is merely on loan and subject to recall by ALPHA WIRE at any time. By taking possession of this document, the recipient acknowledges and agrees that this document cannot be used in any manner adverse to the interests of ALPHA WIRE, and that no portion of this document may be copied or otherwise reproduced without the prior written consent of ALPHA WIRE. In the case of conflicting contractual provisions, this notice shall govern the status of this document. ©2013 ALPHA WIRE - all rights reserved.