

A Donaldson Company

Compact design

Low noise level

Tip extraction iron kit

Standard

Standard

Optional

A WORLD LEADER IN FUME EXTRACTION TECHNOLOGY

Τ1

Single tip extraction for all solder applications.

The T 1 high vacuum unit is designed to extract and filter fumes and debris through small bore hoses and attachments. Ideally suited for soldering iron tip extraction, vac pens and any application requiring close proximity, micro extraction.

Technology



HEPA filter



Advanced carbon

filter (ACF)

technology

ProTECT service

plan





SureCHECK quality standard

Key features of the T 1

High vacuum pumps Standard


3 stage filtration Standard

Contact BOFA at https://bofainternational.com/en/contact/


https://bofainternational.com/en/portal/datasheets/t-1/







Technical specification



6	hch	nic	210	lata
		III C	aιι	iala

	EU	US
Dimensions (HxWxD)	270 x 200 x 185mm	10.63 x 7.87 x 7.28"
Cabinet construction	Powder coated mild steel	Powder coated mild steel
Recommended flow rate with filters fitted (per tip)	22 L/M	22 L/M
Electrical data	230v Single-phase 1~ 50/60Hz Full load current: 0.25amps / 40w	115v 60/50Hz Full load current: 0.46amps / 32w
Noise level	< 48dba (at typical operating speed)	< 48dba (at typical operating speed)
Weight	5kg	11lbs
Pre-filter efficiency	F7 (85% @ 0.8 microns)	F7 (85% @ 0.8 microns)
HEPA filter efficiency	(99.997% @ 0.3 microns	(99.997% @ 0.3 microns
Gas filter	Treated activated carbon	Treated activated carbon
Approvals	UKCA and CE	UKCA and CE

Unit part numbers			
Model	Voltage	Part no.	
T 1 Powder coated	230V	E0142A0000	
T 1 Powder coated	115V	E0141A0000	

Filter part numbers				
Model	Pre-filter part number	Combined filter part number		
Τ1	A1030087	A1030086		

Universal adjustable iron kit part numbers	
Model	Part no.
Non ESD	A1090025
ESD	A1090026

Universal iron kit components (Maximum number of soldering irons: 1)

1. 6mm stainless steel tube 220mm long

5.1 x clear plug

6mm stainless steel tube
110mm long


6. 2.5meters of 6.5mm x 4.5mm silicone hose

3. 5mm stainless steel tube 200mm long

7. Small brass brush

4.4 x E clips

8. Rubber tube to iron strap



	Other languages	
T 1 datasheet <u>Spanish</u>	T 1 datasheet <u>French</u>	
T 1 datasheet <u>German</u>	T 1 datasheet <u>Italian</u>	

Datasheet correct at time of publishing.

Where applicable, the carbon used in BOFA units is capable of removing a wide range of VOC's, however it is the responsibility of the user to ensure the carbon is suitable for their application. For specific applications, please contact us for details.

Think before you print! Please consider the environment before printing this document.