

0.4Nm 4-974-10

TORQUE ADAPTER –

RIGHT SPIN FOR

ERY MOMENT

torque adapter with **fixed** TORQUE

🗘 4 mm

The new mini torque adapters turn every bit holder into a torque screwdriver.

Article-No.

Description

4-970	Bit set with 6 torque adapter
4-970-A	0.1 up to 0.6Nm , in the case, 51pcs. Bit set with 2 torque adapter
4-970-B	0.1 and 0.2Nm , in the case, 47pcs. Bit set with 2 torque adapter
4-970-C	0.3 and 0.4Nm , in the case, 47pcs. Bit set with 2 torgue adapter
	0.5 and 0.6Nm, in the case, 47pcs.

Case also contains:

magnetic ESD bit screwdriver 80 mm, made of aluminium, with screw cap and extension 110 mm, and bit adapter 6.3 mm (1/4) to 4 mm (5/32)

42 bits in the following sizes:

	slot cross-recess torx torx security triangle tri-point square hex pentalobe	1.0, 1.5, 2.0, 2.5, 3.0 PH000, PH00, PH0, PH1 T3, T4, T5 T6, T7, T8, T9, T10, T15 1.6, 2.0, 2.2, 2.3 0, 1 S0, S1 0.9, 1.3, 1.5, 2.0, 2.5, 3.0 P2, P5, P6
	socket wrench	P2, P5, P6 2.5, 3.0, 3.5, 4.0, 4.5, 5.0
(\cdot)	SIM-eject-bit	

Torque adapters are available in sets as well as individally!



4-970-*I*

4-970



TORQUE SCREWDRIVER –

THE RIGHT SPIN FOR EVERY MOMENT



Article-No.	Description
4-563	Mini-torque screwdrivers 0.05 - 0.6 Nm, length 100mm with adapter,
4-930	in transparent box, 2 parts Bit set with torque screwdriver and adapter, in case, 46 pcs.

4-930 also contains:

magnetic ESD bit screwdriver 80 mm, made of aluminium, with screw cap and extension 110 mm, and bit adapter 6.3 mm (1/4") to 4 mm (5/32")

42 bits in the following sizes:

⊕€	slot cross-recess torx	1.0, 1.5, 2.0, 2.5, 3.0 PH000, PH00, PH0, PH1 T3, T4, T5
#	torx security	T6, T7, T8, T9, T10, T15
	triangle	1.6, 2.0, 2.2, 2.3
$\boldsymbol{\heartsuit}$	tri-point	O, 1
	square	S0, S1
	hex	0.9, 1.3, 1.5, 2.0, 2.5, 3.0
۲	pentalobe	P2, P5, P6
0	socket wrench	2.5, 3.0, 3.5, 4.0, 4.5, 5.0
\odot	SIM-eject-bit	



4-930