



Cover profiles



- ▶ For mounting cables
- ▶ To prevent dirt from entering the profile slot
- ▶ Attractive design
- ▶ Soft PVC cover profile for 6 mm slot is provided as a roller
- ▶ Flush with profile
- ▶ An ESD-conductive connection between the cover profile and the strut profile must be ensured through a design solution, e.g. screw

Cover profile, 6 mm slot	Color	Material	ESD	L (mm)		No.
	Colorless, natural	Aluminum, anodized		2000	10	3 842 523 254
	Light gray (RAL 7035)	Soft PVC		10000	1	3 842 542 435
Cover profile, 8 mm slot	Color	Material	ESD	L (mm)		No.
	Colorless, natural	Aluminum, anodized		2000	10	3 842 523 256
	Signal gray (RAL 7004)	PP		2000	10	3 842 548 878
	Black (RAL 9005)	PP		2000	10	3 842 548 879
	Black (RAL 9005)	Hard PVC		2000	10	3 842 501 962
	Light gray (RAL 7035)	Hard PVC		2000	10	3 842 518 375
	Red (RAL 3020)	Hard PVC		2000	10	3 842 518 376
	Yellow (RAL 1023)	Hard PVC		2000	10	3 842 518 377
	Yellow (RAL 6032)	Hard PVC		2000	10	3 842 549 882
	Blue (RAL 5010)	Hard PVC		2000	10	3 842 538 956
	Orange (RAL 2004)	Hard PVC		2000	10	3 842 538 958
	Colorless, transparent	Hard PVC		2000	10	3 842 503 073
Cover profile, 10 mm slot	Color	Material	ESD	L (mm)		No.
	Colorless, natural	Aluminum, anodized		2000	10	3 842 523 258
	Signal gray (RAL 7004)	Hard PVC		2000	10	3 842 548 876
	Black (RAL 9005)	Hard PVC		2000	10	3 842 548 877
	Black (RAL 9005)	Hard PVC		2000	10	3 842 146 901
	Light gray (RAL 7035)	Hard PVC		2000	10	3 842 518 367
	Red (RAL 3020)	Hard PVC		2000	10	3 842 518 368
	Yellow (RAL 1023)	Hard PVC		2000	10	3 842 518 369
	Yellow (RAL 6032)	Hard PVC		2000	10	3 842 549 888
	Blue (RAL 5010)	Hard PVC		2000	10	3 842 538 955
	Orange (RAL 2004)	Hard PVC		2000	10	3 842 538 957
	Colorless, transparent	Hard PVC		2000	10	3 842 191 182