

Ultramas

Enclosure with air vents in the lid and base



UM 52011 L

Order no.: 55520020

* = Available on request.

Characteristics

Colour of enclosure group

Light grey, similar to RAL 7035

Protection class

IP 30

Enclosure Material

ABS; for details see Technical Information

Scope of delivery

2 half-shells, 8 covers, 4 rubber feet, 4 screws

Dimensions

Dimensions

224.2 x 198.9 x 72.4 mm


U

4.5

HP

11

Product drawing



Important!

To compensate for pressure when temperatures change and cause moisture in the enclosure, we recommend that you use a pressure compensation element.

» Additional information

Technical documentation / Downloads

Technical drawings

3D product data in STEP format: Registration necessary

Product drawing in PDF format: 55520020 UM-52011-L.pdf (63.6 KB)

Product drawing in DXF format: 55520020 UM-52011-L.dxf (732.2 KB)

Drawing for mechanical processing: 55520020 UM-52011-L-G.dxf (1.8 MB)

Milling contours are shown here as a DXF file. (Sub D, USB, HDMI, cable glands, ...)

Product information

Ultramas GB.pdf (368.7 KB)

Matching accessories



Extension set, plain, with air vents (L), 3 HP / 9 HP

56020500	AB 02003	3 HP; For UM 32009(L), 62009(L), 52011(L)**
56020000	AB 02009	9 HP; For UM 32009(L), 52011(L), 62009(L)
56020010	AB 02009 L	9 HP; For UM 32009(L), 52011(L), 62009(L)



Front panels, 2 mm, natural-coloured anodised aluminium

56051100	FP 50011	For UM 52011
56052000	FP 50020	For UM 52011 + 1x AB 02009 (L)
56052900	FP 50029	For UM 52011 + 2x AB 02009 (L)



Front panels, ABS, light grey, similar to RAL 7035, embossed on one side

56051110	FPK 50011	For UM 52011
56052010	FPK 50020	For UM 52011 + 1x AB 02009 (L)
56052910	FPK 50029	For UM 52011 + 2x AB 02009 (L)



Tip-up foot set

56012000	UM-AS
----------	-------



Tip-up foot set, collapsible

56012100	UM-ASK	Agate grey
----------	--------	------------



Connection brackets

56002200*	UM-VHH	Agate grey
-----------	--------	------------



Wall brackets for UMP 32018 / 62018

56002000 UM-WLH

Agate grey



Screws (SHR) and distance bolts (DIBLZ) for mounting bosses in plastic enclosures

59006190 SHR Z KA25x6

SD = 2.5 / ND = 2.0 / KD = 4.4