

PB C6 100 PrecisionBits for slotted screws, external hexagon according to DIN ISO 1173 shape C 6,3 (1/4")
 PrecisionBits para tornillos de ranura, hexágono exterior según DIN ISO 1173, forma C 6,3 (1/4")



PB C6.100/1	0.5	3.5	39	26	5	10	7 610733 206049
PB C6.100/2	0.6	4	39	26	5	10	7 610733 017690
PB C6.100/3	0.8	5.5	39	26	7	10	7 610733 017706
PB C6.100/4	1	6.25	39	26	8	10	7 610733 017713
PB C6.100/5	1.2	8	39	26	12	10	7 610733 017720
PB C6.100/6	1.6	10	39	26	16	10	7 610733 017737

PB C6L 100 PrecisionBits for slotted screws, external hexagon according to DIN ISO 1173 shape C 6,3 (1/4")
 PrecisionBits para tornillos de ranura, hexágono exterior según DIN ISO 1173, forma C 6,3 (1/4")



PB C6L.100/0-80	0.4	2.5	95	80	6	10	7 610733 072859
PB C6L.100/1-80	0.5	3.5	95	80	10	10	7 610733 072866
PB C6L.100/2-80	0.6	4	95	80	11	10	7 610733 072873
PB C6L.100/3-80	0.8	5.5	95	80	18	10	7 610733 072880
PB C6L.100/4-80	1	6.25	95	80	20	10	7 610733 072897

PB C6 135 PrecisionBits for slotted screws, external hexagon according to DIN ISO 1173 shape C 6,3 (1/4")
 PrecisionBits para tornillos de ranura, hexágono exterior según DIN ISO 1173, forma C 6,3 (1/4")



PB C6.135/1	0.5	3.5	25	4	10	7 610733 206056
PB C6.135/2	0.6	4	25	4	10	7 610733 015856
PB C6.135/3	0.8	5.5	25	5	10	7 610733 015863
PB C6.135/4	1	6.25	25	6	10	7 610733 015870
PB C6.135/5	1.2	8	25	6	10	7 610733 206063
PB C6.135/6	1.6	10	25	8	10	7 610733 206070

PB C6 190 PrecisionBits for Phillips screws, external hexagon according to DIN ISO 1173 shape C 6,3 (1/4")
 PrecisionBits para tornillos Phillips, hexágono exterior según DIN ISO 1173, forma C 6,3 (1/4")



PB C6.190/0	0	25	5	10	7 610733 206230
PB C6.190/1	1	25	5	10	7 610733 017744
PB C6.190/2	2	25	5	10	7 610733 017751
PB C6.190/3	3	25	5	10	7 610733 017898
PB C6.190/4	4	33	12	10	7 610733 019922