VSEVEN





Charge Cart - 30 Devices - SCHUKO Power

CHGCT30-1E

SKU: CA05072

The V7 Charge Cart allows you to easily secure, store and charge up to 30 Chromebook, laptop, or tablet devices with up to 17" screens. It features an Intelligent charging system, slide-out shelves with flexible, durable device slots, a power supply/cable management system and best of all – it's fully assembled for rapid deployment. Additionally, it features numbered device spaces and corresponding power supply spaces to optimize organization. Made from high-grade 18 gauge cold rolled steel, the Cart also features vented doors with a 3-point key lock mechanism and the option to add your own padlock for extra security.

- Sliding shelves with flexible and durable device dividers allow you to easily store and remove almost any Chromebook, laptop, or tablet
- Efficient intelligent charging system for all of your devices from one plug while protecting circuits from overloading
- Cable management in the front device section and separate rear power section easily organizes power supplies and routes cables to each device
- Both the device section and separate rear power section feature steel doors with 3-point key lock mechanism and the option to add your own padlock for extra security
- 5" high-grade wheels with brakes and direction lock, and a recessed push handle for maximum mobility

General

Sku: CA05072 Model: CHGCT30-1E UPC: 662919107357 Warranty: 5 years Compliance: CE, RoHS Country Of Origin: China Package Type: One Color Package Includes: Charging Cart, 6 ft (1.83 m) Schuko Power Cord, Manual

Color

Color: Black Accent Color: Dark Gray

Design Material: High-grade 18 gauge cold rolled steel

Package Dimensions

Package Dimensions (L/W/H): 25.39 x 24.41 x 50.08 in (645 x 620 x 1272 mm) Shipping Weight: 205.03 lbs (93 kg)

Product Dimensions

Product Dim (L/W/H): 23.62 x 22.83 x 44.37 in (600 x 580 x 1127 mm) Product Weight: 171.96 lbs (78 kg)



Technical

Shelves: Sliding Fully Assembled: Yes Charging System: Intelligent Power Sensing Device Slot Dimensions: 422 × 34.3 × 286 mm (16.61 × 1.35 × 11.25 in) Storage Temperature : -40°C to +60°C Operating Temperature : -10°C to 40°C Storage Humidity: 20% to 90% RH Operating Humidity: 20% to 80% RH AC Cord length: 6 ft (1.83 m) Cable Management: Yes

The data in this publication is for illustration purposes only and does not necessarily represent standards or specifications which must be met by V7. Design and specifications are subject to change without prior notice. Trademarks belong to their respective owners. No responsibility assumed and all liability for damages resulting from use of this information or for any errors or omissions, are disclaimed. Measurement standards and testing conditions, as per manufacturer definitions, are available on request. Last Updated: April 27, 2022 09:55 Page 1