



# Fast, ultra-slim scanner for mobile executives and home users



## Portable document scanner

The lightweight and ultra-portable P-208II scanner's footprint is barely larger than a standard ruler. So it's the perfect choice for mobile executives and home users.

## 10 sheet document feeder, with double-sided scanning

With its 10-sheet ADF, high speed duplex scanning optional Wi-Fi connectivity, this is the ideal scanner to maximise your productivity wherever work takes you.

## Enhanced cloud connectivity

The P-208II is the perfect partner for both Mac and Windows devices. A superb range of desktop software helps you gain maximum productivity from your scanner.

B&W  
SPEED  
8ppm/16ipm

COLOUR  
SPEED  
8ppm/16ipm

DAILY DUTY  
CYCLE  
100 scans/day

AUTOMATIC  
DOCUMENT FEEDER  
10 sheets

## ULTRA SLIM AND LIGHTWEIGHT

### No-compromise mobile scanning

The imageFORMULA P-208II provides travelling executives or office users with impressively fast double-sided colour scanning of up to 16ipm at 200dpi. Maintain productivity on the move with the integrated 10-sheet ADF, which enables easy batch scanning of multiple documents like contracts in a single operation. Weighing just 600g, and little longer or wider than a standard ruler, the P-208II is small and light enough to take anywhere. For maximum flexibility, the P-208II is compatible with Mac and PC computers, as well as Apple iOS and Android mobile devices.\*

\* When connected to the WU10 accessory.

### Intuitive image processing

A rich selection of built-in image processing features help you achieve high quality results. The P-208II offers auto colour detection, text orientation recognition and text enhancement to optimise your scanned images; the full auto mode feature automatically applies the ideal settings for your documents while delivering super-fast results.

### Scan all types of document

The P-208II is the perfect accessory for both home and business use because it's capable of scanning such a wide range of media. Business users can capture regular A4 sized documents like contracts or irregular-sized media like business/embossed cards when they're out of the office.

Home users will also enjoy using the P-208II, because it's perfect for scanning household bills; while the picture mode feature is ideal for accurately scanning old photographs.

### Plug-and-scan convenience with CaptureOnTouch Lite

By using the selectable 'auto-start' feature - just connect with a USB cable and start scanning! CaptureOnTouch Lite software is built into the P-208II so there is no need to download additional drivers or software, it's simply plug-and-scan.



# POWERFUL, INTUITIVE SOFTWARE THAT ENHANCES YOUR PRODUCTIVITY



## Capture OnTouch

Intuitive capture software that makes it quick and simple to achieve premium quality results. CaptureOnTouch incorporates an icon-based user interface with scanning to multiple file formats including PDF, PDF-A, TIFF, JPEG, BMP, PPTX and PNG. CaptureOnTouch can also send captured information directly to data management systems (compatible with both Windows and Mac).

## Capture OnTouch Lite



Offers unique portability and convenience on the move. The software is built into the P-20811 allowing for fast and effortless connectivity without the need to install any drivers or application software (compatible with both Windows and Mac).

## Presto! BizCard

Scan business cards to convert and organise important information into a searchable database (compatible with both Windows and Mac).

### Cloud service plug-ins

The CaptureOnTouch and CaptureOnTouch Lite software includes plug-ins for connecting to cloud and ECM services such as Evernote, Google Drive™, Microsoft SharePoint®, SugarSync, OneDrive (Windows only) and Dropbox.



# Specifications for imageFORMULA P-208II



**Type**  
**Document Reading Sensor**  
**Optical Resolution**  
**Light Source**  
**Reading Side**  
**Interface**  
**Dimensions**  
**Weight**  
**Power Requirements**  
**Power Consumption**  
**Operating Environment**  
**Environmental Compliance**

Desktop Type Sheet Fed Scanner  
 CMOS CIS 2 Line Sensor  
 600 dpi  
 RGB LED  
 Front / Back / Duplex  
 High Speed USB 2.0  
 Tray Closed: 312.5 (W) x 56.5 (D) x 40 (H)mm  
 Tray Opened: 312.5 (W) x 89.5 (D) x 40 (H)mm  
 Approx. 600g  
 Supply from USB (500mA)  
 Scanning: 2.5W, Sleep Mode: 1.5W, Power Turned Off: 0.5W  
 10 - 32.5°C (50 - 90.5°F), Humidity: 25 - 80% RH  
 RoHS and ENERGY STAR

**READING SPEED<sup>1</sup>**  
**(A4, Portrait)**  
**B&W / Greyscale**  
**Colour**

	P-208II	
	Simplex	Duplex
200dpi / 300dpi	8ppm	16ipm
200 dpi	8ppm	16ipm
300dpi	6ppm	12ipm

**DOCUMENT SPECIFICATIONS**

**Width** 50.8 mm - 216 mm  
**Length** 70 - 356mm  
**Thickness** 52 - 209g/m<sup>2</sup> (0.06 - 0.22mm)  
**Card Scanning** 54 x 86 x 1.4mm (Embossed card scanning is supported)  
**Paper Separation** Separation Pad Method  
**Feeder Capacity** 10 sheets (64g/m<sup>2</sup>)

**OUTPUT**

**Resolution** 150 x 150dpi, 200 x 200dpi, 300 x 300dpi, 400 x 400dpi, 600 x 600dpi  
**Mode** Black & White, Advanced Text Enhancement II, 8-Bit Greyscale: (256-Level), 24-Bit Colour

**SPECIAL FEATURES**

Automatic Page Size Detection, Deskew, 3-Dimensional Colour Correction, Auto Colour Detection, Shading Correction, Text Enhancement, Preset Gamma Curve, Scan Panel, Prescan, Image Rotation, Skip Blank Page, Select Scanning Document Side, Scan Area Setting, Text Orientation Recognition, Continuous Scanning, Edge Enhancement, Moire Reduction, Prevent Bleed Through / Remove Background, Contrast Arrangement, Background Smoothing, Shadow Cropping (on / off switchable), Trimming, Apply Corrections Suitable For Photographs, Double Feed Detection (By Length)

**BUNDLED SOFTWARE**

**For Windows OS**

ISIS / TWAIN Driver (Windows XP / VISTA / 7 / 8 / 8.1 / 10)  
 CaptureOnTouch<sup>2</sup>  
 CaptureOnTouch Lite<sup>2</sup>  
 Presto! BizCard Reader  
 Plug-in: Evernote, Google Drive™, Microsoft SharePoint\*, SugarSync, OneDrive and Dropbox

**For Mac OS**

TWAIN Driver  
 CaptureOnTouch<sup>2</sup>  
 CaptureOnTouch Lite<sup>2</sup>  
 Presto! BizCard Reader  
 Plug-in: Evernote, Google Drive™, Microsoft SharePoint\*, SugarSync, Dropbox

**Options**

Canon Wi-Fi Unit WU10  
 Silex C-6600GB Scan-and-Print Server  
 Carry Case

**Consumables Suggested Daily Duty Cycle**

Separation Pad  
 100 scans/day

<sup>1</sup> Scanning speeds may vary depending on the specification of the PC / Mac and the setting of functions.

<sup>2</sup> Software Developer Kits are available through the Canon Business Solutions Developer Programme - [www.canon.europe.com/bsdp](http://www.canon.europe.com/bsdp)

Some images are simulated for clarity of reproduction. All data is based on Canon's standard testing methods. This leaflet and the specifications of the product have been developed prior to the date of product launch. Final specifications are subject to change without notice. ™ and ©, all company and / or product names are trademarks and / or registered trademarks of their respective manufacturers in their markets and / or countries.

## Optional Wi-Fi unit WU10

The Wi-Fi unit WU10 enables wireless scanning to mobile devices without the need to connect via cable to a network point. Businesses can also set-up wireless scanning to desktop PCs with the Wireless Connection Setup Tool and Network Monitor software. The WU10 comes with a rechargeable Lithium-ion battery and when fully charged you can scan up to 400 images. Simply connect via USB to your Canon mobile scanning device and enjoy fast mobile scanning anytime, anywhere.

Scan direct to your iPhone®, iPad® and Android device with the free CaptureOnTouch mobile App. It comes with advanced image processing tools such as automatic size detection, deskew and skip blank page - giving consistently superior image quality results. Download the free CaptureOnTouch Mobile App from Google Play (Android user) or the Apple App Store (iOS user).



**Canon Electronics Inc**  
 Canon.com

**Canon Europe**  
 canon-europe.com

**Canon (UK) Ltd**  
 Woodhatch, Reigate  
 Surrey, RH2 8BF  
 Tel: 01737 220000  
 Fax: 01737 220022  
 canon.co.uk

**Canon Ireland**  
 3006 Lake Drive  
 Citywest, Saggart  
 Co. Dublin, Ireland  
 Tel: 01 2052400 Fax:  
 01 2052525 canon.ie

/CanonUKLtd  
 /CanonUKLtd  
 /CanonEurope