

# NOT JUST SCISSORS AND SHEARS...

## Precision cutting tools made for pros.

The new and improved line of Crescent Wiss shears and scissors offers the performance, strength, and durability professional users need. Every scissor and shear has been upgraded with new features that deliver more comfort, superior results, and longer life. High-performance models feature titanium-coated blades for smooth, powerful cuts and several have a full metal core for maximum strength and durability.

**2X STRONGER**  
**FULL METAL CORE**

**Ergonomic Design**  
Optimizes handle contact points to maximize comfort and control

**Full Metal Core**  
Extends through handle for durability and strength

**Heavy Duty Titanium Coated Blades**  
For powerful cutting and long life

**Control Channel**  
Fits index finger for improved control and more power

**Serrated Bottom Blade**  
Grips material for greater control

**HANDLE XL RINGS**

**SERRATED 10X POWER EDGE**

**USE FOR**  
LANDSCAPING  
FLOORING  
ROOFING  
SIDING  
AND MORE

CW10TM

## HOME & CRAFT SCISSORS

- Precision ground blades feature premium grade stainless steel and are precision engineered for knife-like cutting edges
- Easy adjust pivot bolt allows quick and easy adjustment to fine tune cutting blade tension for optimal cutting performance
- Ambidextrous handle design features symmetrical handle ring contouring for comfortable right or left hand usage
- Stainless steel blades provide corrosion resistance and are harder than steel for durability and tool life
- Straight blades can be sharpened
- Hard plastic handles clean easily
- Lightweight



CATALOG NO.	DESCRIPTION	BARCODE	TOOL LENGTH MM	BLADE LENGTH MM	HANDED	CUTTER HEAD / BLADES	PRODUCT WEIGHT KG	SHELF PACK QTY.	PACKAGING
CW812S	8-1/2 in Home & Craft Scissors	037103333254	216	88	Both	Bottom Serrated	0,204	4	Carded

## ALL PURPOSE SCISSORS

- Precision cut blades feature titanium coated premium grade steel and are precision engineered for knife-like cutting edges
- Offset handle design keeps hands above material for safety and easy table top cuts
- Touch point ergonomics optimize hand and finger contact points in handles to maximize fit, control, and user ergonomics
- Titanium coated blades provide corrosion resistance and are 3X harder than steel for durability and tool life
- Control channel accommodates index finger for increased control and cutting stability
- TPR comfort grip handles are strategically textured using soft-grip TPR to provide best-in-class user comfort and control
- Cuts paper, cardboard, heavy fabric, rope, leather, plastics, and more



CATALOG NO.	DESCRIPTION	BARCODE	TOOL LENGTH MM	BLADE LENGTH MM	HANDED	CUTTER HEAD / BLADES	PRODUCT WEIGHT KG	SHELF PACK QTY.	PACKAGING
CW10T	10 in Titanium Coated All-Purpose Scissors	037103333261	254	100	Right	Smooth	0,209	4	Carded
CW10TL	10 in Titanium Coated All-Purpose Scissors	037103333278	254	100	Left	Smooth	0,209	4	Carded

## SHOP SHEARS FULLMETAL SCISSORS

- Heavy-duty blades feature premium grade stainless steel and are precision engineered for knife-like cutting edges
- Serrated bottom blade grips material as it is being cut for increased cutting control and cleaner cuts
- Titanium coated blades provide corrosion resistance and are 3X harder than steel for durability and tool life
- Control channel accommodates index finger for increased control and cutting stability
- Full metal core extends through the handle for maximum strength and increased durability
- Touch point ergonomics optimize hand and finger contact points in handles to maximize fit, control, and user ergonomics
- Cuts paper, cardboard, heavy fabric, rope, leather, plastics, and more



CATALOG NO.	DESCRIPTION	BARCODE	TOOL LENGTH MM	BLADE LENGTH MM	HANDED	CUTTER HEAD / BLADES	PRODUCT WEIGHT KG	SHELF PACK QTY.	PACKAGING
CW10TM	10 in Titanium Coated All-Purpose Scissors	037103333285	254	100	Right	Bottom Serrated	0,209	4	Carded