# **19" ENCLOSURES**

Designed for electronic and telecommunication equipment to be

installed in 19" cabinets, with the ease of assembly, accessibility

Front & rear internal supports for mounting of trays or PCBs.

and strong construction for an effective installation.

Customisation available; sizes, colour, cutouts,

Secured with 10x screws M4 (8x for 1U)

### 19" Rack Mount Case

1U, 2U & 3U heights

260mm & 360mm depths

mounting and printing

UNIVERSAL ENCLOSURES

HAND HELD CASES

HEAVY DUTY ENCLOSURES

DIN RAIL ENCLOSURES

INTERFACE SUPPORTS

CONTROL STATIONS

DIECAST & METAL ENCLOSURES

DESKTOP & INSTRUMENT CASES

*MULTI-PURPOSE & POTTING BOXES* 

19'' ENCLOSURES

19'' CABINETS

## Contemporary design - 2U & 3U

•

Handles

DEVELOPMENT BOARD ENCLOSURES

CUSTOM SIZED ENCLOSURES

FSPT/CUSTOM SERVICES 
 BLACK
 SILVER
 DESCRIPTION

 C192BHAND
 C192SHAND
 Fits 2U Plate

 C193BHAND
 C193SHAND
 Fits 3U Plate

Handle black RAL 9004 or silver

Can be mounted & disassembled without removing the front

 SPECIFICATION

 Materials
 Front panel 3mm thick aluminium

 Shell 1mm thick steel

 Standard colours
 Clear or black anodised front panel

 Epoxy painted similar to RAL 9002

 Standard unit includes
 Front panel

 Shell-box, rear & lid

 Options (MOQ's apply)
 Custom colours


 Custom dimensions


### Standard 19" Enclosure

SILVER	BLACK	U	DEPTH	HEIGHT	
C19G1263S	C19G1263B	1U	263mm	43.6mm	
C19G1363S	C19G1363B	1U	363mm	43.6mm	
C19G2263S	C19G2263B	2U	263mm	88.1mm	
C19G2363S	C19G2363B	2U	363mm	88.1mm	
C19G3263S	C19G3263B	зU	263mm	132.5mm	
C19G3363S	C19G3363B	ЗU	363mm	132.5mm	

#### 19" Enclosure with handles

SILVER	BLACK	U	DEPTH	HEIGHT
C19G2263SH	C19G2263BH	2U	263mm	88.1mm
C19G2363SH	C19G2363BH	2U	363mm	88.1mm
C19G3263SH	C19G3263BH	зU	263mm	132.5mm
C19G3363SH	C19G3363BH	ЗU	363mm	132.5mm





CC

bsi. 9001 Quality Quality Quality EM 19614 EM 2614 EM 2614



We operate a constant improvement policy, our products are subject to change without notice. +44 (0)1638 716101 info@camdenboss.com www.camdenboss.com