

Product Highlights

Super-Fast Speeds

High speed data transfer rates of up to 1000 Mbps allows HD movie streaming, high-speed Internet access, online gaming and VoIP calls, all at the same time

Simple Setup

Simply plug it directly into a free power outlet¹ and it is ready to be used; no extra cables are needed

Continued Use of Electrical Socket

Passthrough design allows you to continue using your electrical socket by plugging another device into the integrated electrical outlet



DHP-P601AV

PowerLine AV2 1000 HD Gigabit Passthrough Kit

Features

Convenient Home Networking Solution

- Connect two rooms by simply plugging in a pair of adapters
- Share your Internet connection or share files between computers
- Subtle design discreetly blends into your home

Connectivity

- PowerLine data transfer rates of up to 1000 Mbps²
- Gigabit Ethernet Port
- PowerLine interface compatible with IEEE 1901 and HomePlug AV2 standards
- Passthrough socket enables you to plug a device into adapter

Security Features

- Simple Connect button for secure, hassle-free network setup
- 128-bit AES data encryption with key management for secure communications over electrical wiring

Simple Setup

- Plug in to any existing power outlet to create an instant network
- Connect more rooms by simply plugging in additional adapters

The DHP-P601AV PowerLine AV2 1000 HD Gigabit Passthrough Kit comes with two DHP-P600AV PowerLine AV2 1000 HD Gigabit Passthrough Adapters. These adapters use your electrical wiring to extend your home network to places where you currently have no Internet access as your wireless signal is not strong enough to reach (such as a garage or basement). Simply plug one adapter into your existing router to turn any power outlet in your home into an Internet connection and then plug the other adapter into the room you want to extend your connection to.

These PowerLine adapters also feature an extra passthrough power socket to ensure that your electrical outlet remains available for use by another device while the PowerLine adapter is plugged into the socket. The Passthrough socket features noise filtering which helps prevent signal noise from any electrical device plugged into the socket from affecting your PowerLine connection.

Data Transmission Over Electrical Wiring

The D-Link DHP-P601AV PowerLine AV2 1000 HD Gigabit Passthrough Kit turns every power socket into a possible network connection to access digital media devices, game consoles, network printers, computers and network storage devices throughout your home. Compliance with the HomePlug AV2 standard and backward compatibility with the HomePlug AV standard ensure that the DHP-P601AV can be used with older PowerLine devices.

Ideal For Bandwidth-Intensive Applications


The DHP-P601AV is capable of delivering data transfer rates of up to 1000 Mbps². This rapid transmission speed makes it ideal for bandwidth-intensive applications, guaranteeing smooth HD video streaming, VoIP calls, and lag-free online gaming. In addition, it prioritises Internet traffic to help ensure that whatever movie or music you're streaming doesn't skip or stutter while you're web surfing and downloading files at the same time. Now you can experience high-quality multimedia streaming throughout your home, all through your existing electrical wiring.

Convenient Setup and Secure Operation

The DHP-P601AV PowerLine adapters plug directly into your home power sockets and do not require any additional cables. Extend your home network by connecting multiple devices in the furthest corners of your home or attach a switch or wireless access point to the adapter for additional connectivity. For convenient setup, an encryption key can be quickly configured with the push of a button. The adapters implement 128-bit AES data encryption to protect the network from unauthorised wire-tapping. With hassle-free plug and play installation, the DHP-P601AV is an ideal solution to create a wall-to-wall home network.

Saves Power Automatically

The DHP-P601AV incorporates a power saving mode that automatically places the adapter in sleep mode if no data transmission or reception occurs over a certain period of time, reducing power usage by more than 85%. This helps you save energy automatically without sacrificing performance.



Technical Specifications

General

Powerline Interface	• Power plug (country-dependent)
Ethernet Interface	• RJ-45 Gigabit Ethernet LAN port

Functionality

Standards	• IEEE 802.3 • IEEE 802.3u	• IEEE 1901 • HomePlug AV2
Security	• 128-bit AES data encryption	
LEDs	• Power • Ethernet	• PowerLine
Powerline Modulation Scheme	• OFDM Symbol Modulation	
Powerline Frequency Band	• 2 MHz to 86 MHz	
Data Rate	• Ethernet: 10/100/1000 Mbps (auto negotiation)	• PowerLine: Up to 1000 Mbps (PHY rate)

PowerLine AV2 1000 HD Gigabit Passthrough Kit

Physical	
Dimensions	• 113.49 x 58.48 x 37.8 mm (4.47 x 2.30 x 1.49 inches) each adapter
Weight	• 195 grams (0.42 lbs) each adapter
Power	• Input: 100 to 240 V AC, 50/60 Hz
Power Consumption	• 3.7 W maximum (each adapter)
Temperature	• Operating: 0 to 40 °C (32 to 104 °F) • Storage: -20 to 65 °C (-4 to 149 °F)
Humidity	• Operating: 10% to 90% non-condensing • Storage: 5% to 95% non-condensing
Certifications	• CE • CE/LVD

¹ Power outlets and electrical wiring must all be part of the same electrical system. Certain electrical conditions in your home, such as wiring condition and configuration, may affect the performance of this product. Additional D-Link PowerLine AV series products are required to add new devices to the network. A minimum of two D-Link PowerLine AV series products are required to create a network. Connecting this product to a power strip with a surge protector may adversely affect the performance of this product. For best results, plug the adapter directly into a wall outlet.

² Maximum throughput is based on theoretical transmission PHY rate. Actual data throughput will vary. Network conditions and environmental factors, including volume of traffic and network overhead, may lower actual data throughput rate. Interference from devices that emit electrical noise, such as vacuum cleaners and hair dryers, may adversely affect the performance of this product. This product may interfere with devices such as lighting systems that have a dimmer switch or a touch-sensitive on/off feature, short wave radios, or other PowerLine devices that do not follow the HomePlug AV standard.



For more information: www.dlink.com

D-Link European Headquarters. D-Link (Europe) Ltd., D-Link House, Abbey Road, Park Royal, London, NW10 7BX.
 Specifications are subject to change without notice. D-Link is a registered trademark of D-Link Corporation and its overseas subsidiaries.
 All other trademarks belong to their respective owners. ©2015 D-Link Corporation. All rights reserved. E&OE.

Updated May 2015

