

# USB-C™ Universal Quad 4K (QV4K) Docking Station with 100W Power Delivery

DOCK570EUZ



## Description

Boost productivity and performance with the world's first enterprise-class universal docking station to deliver four 4K extended displays. Ideal for large enterprises – the Targus USB-C™ Universal Quad 4K (QV4K) Docking Station maximises workstation viewing. Dual DisplayLink® DL-6910 chip technology supports up to four DisplayPort (3840 x 2160 p60) or HDMI (3840 x 2160 p50) displays. The docking station includes numerous additional ports to connect your essential USB 3.0 peripherals and Ethernet network.

This sleek dock helps reduce clutter by providing the ease of a single connection for key peripherals like your mouse, keyboard and more. Its rubberised, padded bottom protects against scratches, while the VESA bracket mounting provision allows for use of the Targus VESA Mount Bracket (ACX003GLZ – sold separately) to hold your dock behind your display for even greater space savings. Your most advanced configurations become easy with compatibility across virtually any laptop and most standard peripherals including Thunderbolt 3™, Display Port Alt-Mode, and USB 3.0, 3.1 and Type-C devices. Charging tips and a USB-C to USB-A adapter included to make this dock compatible with a variety of major laptop brands.

## Supports DisplayPort and HDMI Monitors

Your workstation has never been more powerful with a high-performance quad-monitor dock that supports full 4K (3840 x 2160 p60) resolution or DisplayPort (3840 x 2160 p60) on all four displays as well as viewing modes for two and three monitors. The eight available video out ports allow you to decide between HDMI or DP++ display options to ensure compatibility for your configuration.

## Powering Your Devices

The Universal USB-C™ Quad 4K Docking Station with 100W Power Delivery is the first quad-docking solution designed to keep your devices running no matter how long your day is. A simple front-panel blue light lets you know when power is connected, and a switch allows you to turn your power on or off in a snap. Offering 100W USB power delivery on PD 2.0, you can power laptops and larger devices through your dock, further reducing your clutter and making it easy to keep going all day.

## Onboard USB 3.0 for Advanced Peripherals and Charging

Four USB 3.0 ports make it easy to customise workspaces with the latest keyboards, external drives and other essential peripherals. Efficient charging is close at hand with one powered USB 3.0 port for keeping smartphone, tablet or other devices powered up and ready to go.

## Features

- Supports four 4K displays via four DisplayPort (3840 x 2160 p60) or four HDMI (3840 x 2160 p50) ports
- Thunderbolt™ 3 compatible
- 1 USB-C 3.0 port with power (100W non-PD)
- 4 USB 3.0 ports (1 fast charging) connect essential peripherals
- 1 Gigabit Ethernet port
- 1 3.5mm combo Audio In/Out for mics, speakers and earphones with Apple and Nokia headset auto-detection
- Includes USB-C to USB-A Cable to make USB-A laptops compatible with Targus USB-C™ docking stations
- Power tips included to power Acer®, ASUS®, Compaq®, Dell™, Fujitsu®, Gateway®, HP®, IBM/Lenovo™ and Toshiba
- Works With: PCs, Macs, Chromebooks and Android Devices, and Windows® (10/8.1/7), Mac® OS X (10.12/10.11/10.10), Android™ (5.0 or later), Chrome (R51 or later), Ubuntu Linux
- Limited 3-Year Warranty

## Specifications

Colour	Grey
Compatibility	Windows® (10/8.1/7), Mac® OS X (10.12/10.11/10.10), Android™ (5.0 or later), Chrome (R51 or later), Ubuntu Linux
Warranty	Limited 3-Year Warranty
Exterior Dimensions	26 x 8.5 x 17.9 cm
Weight	2 kg
Country of Origin	China
EAN Barcode	5051794028362

[targus.com/uk](http://targus.com/uk)

Features and specifications are subject to change without notice.  
All trademarks and registered trademarks are the property of their respective owners. ©2019 Targus.