



# Wallaby™ Self-Service Stands

For Point of Sale or  
Self-Service Application



**Flexible & Configurable**



**2-Year Warranty**



**Commercial Grade**

## Product Overview

Wallaby Self-Service Stands are available in two configurations - countertop or floor mounted, both help to simplify installation of interactive experiences in public, high-traffic environments. The sleek, space-saving stands are designed to house a touchscreen in portrait or landscape, a variety of peripherals, an expansion module and a standard 3" printer in a secure, cable free installation.

By introducing these products into settings where engagement is essential, companies can create a unified approach to any customer experience in point of sale and self-service including applications for endless aisle, price verification, loyalty programs, brand experience, fitting rooms, patient check-in, time clock applications and more. With the Wallaby stands, you can "stand up" a 15 inch to 22 inch Windows or Android based self-service touchscreen solution with ease, complete with payment and printing capabilities.

### Compatible Peripherals

- EMV
- MSR
- Barcode Scanner
- Status Light
- NFC
- Fingerprint Reader

## Wallaby Self-Service Stands

Specifications		
Model	Wallaby Self-Service Countertop Stand E796783 (for I-Series 2/3 for Android, I-Series 2 for Windows) E421137 (for I-Series 4 for Android)	Wallaby Self-Service Floor Stand E796965 + E797162 (for I-Series 2/3 for Android, I-Series 2 for Windows) E421325 + E797162 (for I-Series 4 for Android)
Color	Black / Silver	
Compatibility	15" I-Series Android/Windows in portrait and landscape 22" I-Series Android/Windows in portrait and landscape	
Printer Compatibility	Epson TM-T88, M30 (requires E797921 printer tray) Star TSP100, TSP654 Bixolon SRP-350	
EMV Compatibility	<p>For E796783/E796965 + E797162: Verifone MX915 - E798125, Verifone E355 - E201088, Verifone MX925 - E352169, Verifone P400 - E906829 Ingenico iSC250 - E798125, Ingenico RP757 - E920661, Ingenico iPP320/350/315 - E699053, Ingenico ICMP - E200465, Ingenico RP457C (Bluetooth) - E710930, Ingenico RP457C (Audio Jack) - E586981, Ingenico LANE3000 - E410697 MagTek eDynamo - E375343</p> <p>For E421137/E421325 + E797162: Verifone MX915 - E458992, Verifone M400 - E458992, Verifone MX925 - E352169, Verifone P400 - E906829 Ingenico iSC250 - E458992, Ingenico RP757 - E920661, Ingenico iPP320/350/315 - E458797, Ingenico RP457C (Bluetooth) - E710930, Ingenico RP457C (Audio Jack) - E586981, Ingenico LANE3000 - E458605 Square Terminal - E458992 MagTek eDynamo - E375343</p>	
Weight	Unpackaged: 24.69 lbs / 11.2 kg Packaged: 28.17 lbs / 12.78 kg	Unpackaged: E796965/ E421325: 40.78 lbs / 18.5 kg; E797162: 27.34 lbs / 12.4 kg Packaged: E796965/ E421325: 49.44 lbs / 20.61 kg; E797162: 30.64 lbs / 13.9 kg
Dimensions	11.6" x 9.1" x 17" / 295mm x 230mm x 431.96mm	22.1" x 14.6" x 47" / 562.43mm x 370mm x 1192.8mm
Shipping Dimensions	25.35" x 12.08" x 11.93" / 644mm x 307mm x 303mm	E796965/ E421325: 50.55" x 12.44" x 12.44" / 1284mm x 316mm x 316mm E797162: 28.58" x 19.13" x 4.56" / 726mm x 486mm x 116mm
Temperature	Operating: 0° C to 40° C (32° F to 104° F) Storage: -20° C to 60° C (-4° F to 140° F)	
Humidity (non-condensing)	Operating: 20% - 80% Storage: 10% - 90%	
ADA Compliant	Yes	
Warranty	2-year standard warranty	
What's in the Box	QIG Small black tie-wrap, x3 Screws for Countertop Stand (refer to MS drawing for details) 4-Port USB-A 3.0 Hub Head Assembly Countertop base Mounting display bracket for Android I-Series Mounting display bracket for Windows I-Series	QIG Small black tie-wrap, x3 Hook and Loop Cable Tie with Buckle, x3 Screws for Floor Stand (refer to MS drawing for details) 4-Port USB-A 3.0 Hub Floor-Head Assembly Floor base Mounting display bracket for Android I-Series Mounting display bracket for Windows I-Series

## Ordering Information

Part Number	Part Description	Compatibility	Availability
E796783	Wallaby Self-Service Countertop Stand	Android I-Series 2/3, Windows I-Series 2	US, Canada, EMEA, Japan, China
E796965	Wallaby Self-Service Floor Top	Android I-Series 2/3, Windows I-Series 2	US, Canada, EMEA, Japan, China
E797162	Wallaby Self-Service Floor Base	Android I-Series 2/3/4, Windows I-Series 2	US, Canada, EMEA, Japan, China
E421137	Wallaby Self-Service Countertop Stand	Android I-Series 4	US, Canada, EMEA, Japan, China
E421325	Wallaby Self-Service Floor Top	Android I-Series 4	US, Canada, EMEA, Japan, China

## Accessory Ordering Information

Part Number	Part Description
E351978	Display mounting bracket for Android I-Series
E244791	Display mounting bracket for Windows I-Series
E797921	Epson M30 Printer Tray Bracket

Learn more about Elo at [EloTouch.com](https://www.elotouch.com).

### Americas

Tel +1 408 597 8000  
elosales.na@elotouch.com

### Europe (EMEA)

Tel +32 16 930 136  
EMEA.Sales@elotouch.com

### Asia Pacific

Tel +86 (21) 3329 1385  
EloAsia@elotouch.com

Elo reserves the right to change or update, without notice, any information contained herein; to change, without notice, the design, construction, materials, processing or specifications of any products; and to discontinue or limit production or distribution of any products. Elo, the Elo logo and Wallaby are either trademarks or registered trademarks of Elo Touch Solutions, Inc. All other trademarks are the property of their respective owners. © 2022 Elo Touch Solutions, Inc. All rights reserved. 22011AES00127

