

ergotron®

moving you forward

Lockable Tablet Mount

- Theft deterrence achieved through the use of a mechanical lock
- Position your tablet within your digital workflow by installing cradle on an Ergotron mount (compatible with many Ergotron Arms such as the LX, Neo-Flex® and MX Mini)
- Adjustable contact points keep ports free, providing access to power buttons, power cords, USB, HDMI, and docking connectors
- Sliding brackets accept most tablet sizes, from iPad mini to iPad Pro, with or without case
- Easily remove tablet from cradle when you need to go (when used without key)
- Holds tablet in portrait or landscape mode
- Robust metal and composite design dampens shock and vibration



SECURE YOUR TABLETS AT THE POINT-OF-SALE, BACK OFFICE OR RETAIL KIOSK

Convert a monitor mount to securely hold a tablet. The locking interface makes it the perfect solution for info kiosks, interactive restaurant ordering, public signage or healthcare patient entertainment—anywhere theft deterrence is a priority.

Works with most popular tablets, including Apple® iPad®, Microsoft® Surface® and Samsung® Galaxy®.

Lockable Tablet Mount



Part # (color)	45-460-026 (silver)
Includes	Tablet cradle with lock, VESA mounting thumb and security screws, M4 hex security wrench, 2 keys
Typical LCD Size	Typical screen size 7.9–13" Allowable Tablet Dimensions: 5.3–8.7" (13,5–22 cm) x 7.9–12" (20–30,6 cm) Maximum tablet depth 0.9" (2,3 cm)
<small>LCD SIZE IS APPROXIMATION. DIMENSION IS DIAGONAL MEASUREMENT OF SCREEN. LCD SIZE MAY BE EXCEEDED AS LONG AS SCREEN WEIGHT DOES NOT EXCEED MAXIMUM WEIGHT CAPACITY OF THE MOUNT.</small>	
Weight Capacity	≤ 5 lbs (2,3 kg)
VESA	VESA MIS-D, 75/100 (hole pattern 100 x 100 mm & 75 x 75 mm). Attaches to monitor mounts using this VESA interface
Product Weight	1 lbs (0,45 kg)
Shipping Weight	2 lbs (0,8 kg)
Shipping Dimensions	11" x 7.5" x 3.5" (28 x 19 x 9 cm)
Warranty	5 years

Download additional resources at ergotron.com.
 For more information:
 NORTH AMERICA: 800.888.8458 / +1.651.681.7600 / insidesales@ergotron.com
 EMEA: +31.33.45.45.600 / info.eu@ergotron.com
 APAC: apaccustomerservice@ergotron.com
 Custom: custom@ergotron.com

© Ergotron, Inc. 03.17.2020
 Literature made in the U.S.A.
 Content subject to change.
 Ergotron devices are not intended to cure, treat, mitigate or prevent any disease.
 Patent information available at www.ergotron.com/patents.

