

PRODUCT SPECIFICATION

GP Portable PowerBank Model : MP05MA

Revision History

Revision	Date	Initiator	Reason for Change
0.0	22 Dec 2017		First Release
0.1	15 Jan 2018		Update product line dwg & re-charging time

Prepared By	Approved By
CC Li	Kevin Chan
Date: 15 Jan 2018	Date: 15 Jan 2018
Date. 15 Jan 2010	Date. 15 Jan 2010

GPI International Limited


7/F, Building 16W, 16 Science Park West Avenue Hong Kong Science Park, New Territories, Hong Kong, Tel: (852) 2484 3333 Fax: (852) 24805912 Email: gpii@goldpeak.com Website: <u>http://www.gpbatteries.com</u>

Member Gold Peak Group Manufacturer reserves the right to alter or amend the design, model and specification without prior notice.



Product Specification

Model no.: MP05MA



Product Name		GP MP05MA Portable PowerBank with Type C port
Description		Back up power for USB powered electronic devices
		(e.g. smartphones, tablet PCs)
Battery Rating	:	Lithium Polymer 3.7V 5000mAh 18.5Wh
Micro USB Port	:	Input 1A / 5V DC
USB Port (x2)	:	Output 2.1A / 5V DC (Total)
Application	:	Charge USB powered electronic devices
Recharging Time	:	5.5 hours by 5V/1A;
Discharging Time	:	1 hours 15 mins at 2.1A
		(The discharging time may vary for different devices)
Operation Temperature	:	5°C to 40°C
Safety protection	:	1) Over current protection
		2) 1 st Level over charging & discharging protection
		3) 2 nd Level over charging & discharging protection

Member Gold Peak Group Manufacturer reserves the right to alter or amend the design, model and specification without prior notice.

GP Batteries

Product Specification

Model no.: MP05MA

- 4) Short circuit protection
- 5) Over temperature protection
- 6) Under temperature protection
- 7) Loop back protection

LED Indication : Charging & Discharging the Portable PowerBank

Table 1

Charging & Discharging Condition	LED Indicator
Charging	Last LED flashing
Discharging	Refer to battery status (Table 2)
Fully charged	All LEDs On
Errors	1 st LED Fast flashing & then off

Press button to show battery status :

Table 2

Battery Strength	LED indicator
Good	Four LED on
Good to average	First Three LED on
Average	First Two LED on
Weak	One LED on
No Power	No LED

Dimensions	:	135.5 (L) x 70 (W) x 10 (H) mm (+/- 0.5mm)
Weight	:	147g (approx.)
Certification	:	CE, FCC, UN38.3, IEC62133 (Pending), IEC60950 (Pending)
Warranty Period	:	12 months from ex-factory date

Member Gold Peak Group

Manufacturer reserves the right to alter or amend the design, model and specification without prior notice.