

PRODUCT SPECIFICATION

GP Portable PowerBank Model : MP15MA

Revision History

Revision	Date	Initiator	Reason for Change
0.0	22 Dec 2017		First Release
0.1	15 Jan 2018		Update product line dwg & re-charging time

Prepared By	Approved By
CC Li	Kevin Chan
Date: 15 Jan 2018	Date: 15 Jan 2018


GPI International Limited

7/F, Building 16W, 16 Science Park West Avenue Hong Kong Science Park, New Territories, Hong Kong, Tel: (852) 2484 3333 Fax: (852) 24805912 Email: gpii@goldpeak.com

Website: http://www.gpbatteries.com

GP Batteries

Product Specification



Product Name GP MP15MA Portable PowerBank with Type C port

Description Back up power for USB powered electronic devices

(e.g. smartphones, tablet PCs)

Battery Rating Lithium Polymer 3.7V 15000mAh 55.5Wh

Micro USB Port Input 2A / 5V DC

USB Port (x2) Output 2.4A / 5V DC

USB Type C Input 3A / 5V DC; Output: 3A / 5V DC

Total 3A for 3 output ports

Charge USB powered electronic devices Application

Recharging Time 6.5 hours by 5V/3A at USB-C port;


Discharging Time 3 hours at 3A via USB-C port

(The discharging time may vary for different devices)

Operation Temperature : 5°C to 40°C

1) Over current protection Safety protection

2) 1st Level over charging & discharging protection



Manufacturer reserves the right to alter or amend the design, model and specification without prior notice.

GP Batteries

Product Specification

3) 2nd Level over charging & discharging protection

Model no.: MP15MA

- 4) Short circuit protection
- 5) Over temperature protection
- 6) Under temperature protection
- 7) Loop back protection

LED Indication : Charging & Discharging the Portable PowerBank

Table 1

Charging & Discharging Condition	LED Indicator
Charging	Last LED flashing
Discharging	Refer to battery status (Table 2)
Fully charged	All LEDs On
Errors	1 st LED Fast flashing & then off

Press button to show battery status:

Table 2

Battery Strength	LED indicator
Good	Four LED on
Good to average	First Three LED on
Average	First Two LED on
Weak	One LED on
No Power	No LED

Dimensions : $135.5 (L) \times 70 (W) \times 18 (H) mm (+/- 0.5mm)$

Weight : 320g (approx.)

Certification : CE, FCC, UN38.3, IEC62133 (Pending), IEC60950 (Pending)

Warranty Period : 12 months from ex-factory date

Member
Gold Peak Group

Manufacturer reserves the right to alter or amend the design, model and specification without prior notice.