

# ACCESSORIES

Order symbol      Description

## Back Panels (Galvanized steel, sheet thickness 1,5 mm)

EKHVT	5.8 x 5.8 inch ▪ 148 x 148 mm
EKJVT	9.4 x 5.8 inch ▪ 238 x 148 mm
EKMVT	13.3 x 5.8 inch ▪ 338 x 148 mm
EKOVT	9.4 x 9.4 inch ▪ 238 x 238 mm
EKPVT	13.3 x 9.4 inch ▪ 338 x 238 mm
EKTVT	20.4 x 9.4 inch ▪ 518 x 238 mm
EKUVT	20.4 x 13.3 inch ▪ 518 x 338 mm



## DIN-35 Mounting rails (Galvanized steel, rail height 7,5 mm)

EKV 12	1.4 x 6.3 inch ▪ 35 x 160 mm
EKV 22	1.4 x 9.3 inch ▪ 35 x 235 mm
EKV 32	1.4 x 13.2 inch ▪ 35 x 335 mm
EKV 50	1.4 x 19.7 inch ▪ 35 x 500 mm



## Mounting rail accessories

MSM PT 5x10	Mounting screw
MB 10686	Kit of 2 spacers including screws ▪ (15/34 mm)

## DIN rail frames

MS PROF 19	DIN rail frames
MS PROF 28	DIN rail frames
MS PROF 38	DIN rail frames
MS PROF 56	DIN rail frames
EKT PROF 56	DIN rail frames



## Extension frames (Polycarbonate, PUR Gasket)

EKJZR	10.9 x 7.4 x 2 inch ▪ 278 x 188 x 50 mm
EKMZR	14.9 x 7.4 x 2 inch ▪ 378 x 188 x 50 mm
EKOZR	10.9 x 10.9 x 2 inch ▪ 278 x 278 x 50 mm
EKPZR	14.9 x 10.9 x 2 inch ▪ 378 x 278 x 50 mm
EKTZR	22 x 10.9 x 2 inch ▪ 558 x 278 x 50 mm
EKUZR	22 x 14.9 x 2 inch ▪ 558 x 378 x 50 mm



## Hinges and wall mounting

MB 10622	PC Hinge set, 1 pair ▪ incl. screws and drill template
MB 10523	Blind plug for cover corner on hinged side when cover screws are not used
MB 10674	Mounting foot kit (4 pcs) ▪ incl. screws



## Cover screws

HS 10255	Wing head ▪ for 30 mm cover
CS 10256	Cross head ▪ for 30/100 mm cover
SS 10535	Slotted head (sealable) ▪ for 30 mm cover
SS 10544	Slotted head (quick-lock) ▪ for 30/100 mm cover
HS 10533	Wing head (quick-lock) ▪ for 30 mm cover
HS 10532	Quick-locking wing head (hinged) ▪ for 30 mm cover
MB 10534	Threaded bushing ▪ to be ordered separately with quick-lock screws
SS 10563	Cross head ▪ for 80 mm cover
HS 10562	Wing head ▪ for 80 mm cover
DS 10581	Triangle head ▪ for 30/80/100 mm cover
MB 10673 SET	Triangular key ▪ for cover screw DS 10581
SS 10256-4	Set of 4 cross head screws ▪ for 30/100 mm cover
SS 10256-6	Set of 6 cross head screws ▪ for 30/100 mm cover
SS 10563-4	Set of 4 cross head screws ▪ for 80 mm cover

