

The Jabra Engage 75 Engineered to be the world's most powerful professional wireless headsets*

The Jabra Engage 75 is an entirely new class of DECT wireless professional headsets engineered to boost customer satisfaction.

Industry-leading professional wireless performance. Better customer connections.

Provides superior wireless connectivity to a range of up to 150m/490ft, enabling up to 3x more users to operate in the same office space - with no loss in connection quality.1

Crystal-clear calls. Enhance the customer experience.

Advanced noise-cancelling microphone and enhanced speakers deliver crystal-clear calls even in noisy offices. Meets Skype for Business Open Office requirements.²

More talk time, less interruption. Increase productivity.

Up to 13 hours talk time³ and a busylight that acts as a do-notdisturb sign for colleagues.

Any call, from any device. Increase availability for calls.

Connect to up to five devices simultaneously, increasing your team's availability for customer calls. Can connect to 2 USB devices (softphone and/or desk phone), 2 Bluetooth® devices and 1 analog desk phone.

Choice of wearing styles. Support different workstyles.

With stereo, mono and lightest-in-category convertible models, there's a Jabra Engage for everyone.


- *Relates to Jabra Engage 75/65 Stereo and Mono variants February 19, 2018. See facts on Jabra.com/commercial-claims ¹ Find details on page 2 ² Variant dependent ³ Dependent on usage




Jabra Engage 75 Datasheet

Getting started

Connect to power






First, connect the desk phone and PC cables to the base. For information on your specific phone, refer to http://www.jabra.com/compatibilityguide


Then plug the base into a power supply, and then scroll to the Setup Wizard in the menu. The Setup Wizard will help you connect to your computer, smartphone, or desk phone.

How to use

Stereo and Mono



Convertible



How to wear Mono Headband Neckband Convertible EarGels Earhook wearing style Neckband









Features	Jabra Engage 75 Stereo	Jabra Engage 75 Mono	Jabra Engage 75 Convertible
Wireless capacity NA/EU – wideband ¹	70/145	70/145	70/145
Wireless capacity NA/EU – narrowband ²	95/190	95/190	95/190
Wireless range (up to – meters/feet)	150/490	150/490	100/330
Talk time (up to – hours) ³	13	13	9
Fast charge – from 0-40% (minutes)	30	30	30
Emergency charging	Yes	Yes	Yes
Connectivity – how many devices	5 ⁴	5 ⁴	54
Wireless technology	DECT	DECT	DECT
Secure DECT (level)	С	С	С
Intelligent volume control (speech level normalization and balanced voice)	Yes	Yes	Yes
User sound protection (PeakStop [™] , Noise@Work, Intelligent Acoustic Shock, IntelliTone 2.0)	Yes	Yes	Yes
Directional noise cancelling microphone	Yes	Yes	Yes
Microphone (G-MOS, Tx, CC)	4.3	4.3	3.8
Speaker (P-MOS, Rx, Silent)	4.4	4.4	3.9
Meets Skype for Business Open Office requirements	Yes	Yes	No
Music streaming via Bluetooth®	Yes	Yes	Yes
Boom arm adjustable	270°	270°	360°
Busylight	Yes	Yes	Yes
Wearing styles	Stereo	Mono ⁵	Choice of earhook, neckband or headband
Headset weight (g)	90	64	18

Compatibility

For compatibility information go to ${\bf Jabra.com}$









 $^{^1}$ DECT capacity, number of theoretical users in wideband. Actual numbers may vary 2 DECT capacity, number of theoretical users in narrowband. Actual numbers may vary 3 Dependent on usage 4 Can connect to 2 USB devices (softphone and/or desk phone). 2 Bluebooth 6 devices and 1 analog deskphone 5 Engage 75 Mono: comes with neckband accessory 6 Softphone certified, desk phone in progress