

### **PRODUCT SPECIFICATION**

### GP Portable PowerBank Model : MP10MA

**Revision History** 

Revision	Date	Initiator	Reason for Change
0.0	22 Dec 2017		First Release
0.1	15 Jan 2018		Update product line dwg & re-charging time

Prepared By	Approved By
CC Li	Kevin Chan
Date: 15 Jan 2018	Date: 15 Jan 2018

**GPI International Limited** 


7/F, Building 16W, 16 Science Park West Avenue Hong Kong Science Park, New Territories, Hong Kong, Tel: (852) 2484 3333 Fax: (852) 24805912 Email: gpii@goldpeak.com Website: <u>http://www.gpbatteries.com</u>

Member Gold Peak Group Manufacturer reserves the right to alter or amend the design, model and specification without prior notice.



## **Product Specification**

### Model no.: MP10MA



Product Name	:	GP MP10MA Portable PowerBank with Type C port
Description	:	Back up power for USB powered electronic devices
		(e.g. smartphones, tablet PCs)
Battery Rating	:	Lithium Polymer 3.7V 10000mAh 37Wh
Micro USB Port	:	Input 2A / 5V DC
USB Port (x2)	:	Output 2.4A / 5V DC
USB Type C	:	Input 3A / 5V DC ; Output : 3A / 5V DC
		Total 3A for 3 output ports
Application	:	Charge USB powered electronic devices
Recharging Time	:	4.5 hours by 5V/3A at USB-C port;
Discharging Time	:	2 hours at 3A via USB-C port
		(The discharging time may vary for different devices)
Operation Temperature	:	5°C to 40°C
Safety protection	:	1) Over current protection
		2) 1 <sup>st</sup> Level over charging & discharging protection

# **GP** Batteries

### **Product Specification**

### Model no.: MP10MA

- 3) 2<sup>nd</sup> Level over charging & discharging protection
- 4) Short circuit protection
- 5) Over temperature protection
- 6) Under temperature protection
- 7) Loop back protection

#### LED Indication : Charging & Discharging the Portable PowerBank

Table 1

Charging & Discharging Condition	LED Indicator
Charging	Last LED flashing
Discharging	Refer to battery status (Table 2)
Fully charged	All LEDs On
Errors	1 <sup>st</sup> LED Fast flashing & then off

### Press button to show battery status :

Table 2

Battery Strength	LED indicator
Good	Four LED on
Good to average	First Three LED on
Average	First Two LED on
Weak	One LED on
No Power	No LED

Dimension	:	135.5 (L) x 70 (W) x 13.5 (H) mm (+/- 0.5mm)
Weight	:	233g (approx.)
Certification	:	CE, FCC, UN38.3, IEC62133 (Pending), IEC60950 (Pending)
Warranty Period	:	12 months from ex-factory date

Member

Member Gold Peak Group Manufacturer reserves the right to alter or amend the design, model and specification without prior notice.