

# Rittal – The System.

Faster – better – everywhere.

► **Small enclosures KX  
Terminal box KX,  
sheet steel, without  
gland plate – KX  
1500.000**

Date : Aug 6, 2021

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# Small enclosures KX Terminal box KX, sheet steel, without gland plate – KX 1500.000

created: 06.08.2021 build on [www.rittal.com/uk-en](http://www.rittal.com/uk-en)



## Product description

<b>Description:</b>	The small enclosure KX, terminal box KX, without a gland plate allows for flexible interior installation while maintaining a high protection category.
<b>Material:</b>	Enclosure: Sheet steel Cover: Sheet steel, all-round foamed-in PU seal
<b>Surface finish:</b>	Enclosure and cover: Dipcoat primed, powder-coated on the outside, textured paint
<b>Colour:</b>	RAL 7035
<b>Protection category IP to IEC 60 529:</b>	IP 66
<b>Protection category NEMA:</b>	NEMA 1, 3R, 4, 12
<b>Type rating to UL 50E:</b>	Type 1, 3R, 4, 12
<b>IK Code:</b>	IK08
<b>Supply includes:</b>	Enclosure with cover Mini cam lock
<b>Basic material:</b>	Sheet steel

## Product description

<b>Dimensions:</b>	Width: 150 mm Height: 150 mm
--------------------	---------------------------------

Depth: 120 mm

<b>Material thickness:</b>	Enclosure: 1.25 mm Cover: 1.25 mm
<b>No. of mini cam locks:</b>	4
<b>Packs of:</b>	1 pc(s).
<b>Weight/pack:</b>	1.46 kg
<b>EAN:</b>	4028177816145
<b>Customs tariff number:</b>	73269098
<b>ETIM 7.0:</b>	EC000261
<b>ETIM 6.0:</b>	EC000261
<b>eCl@ss 8.0/8.1:</b>	27180101
<b>eCl@ss 6.0/6.1:</b>	27180101
<b>Product description:</b>	KX Terminal box, WHD: 150x150x120 mm, sheet steel, without mounting plate, with cover, without gland plate

## Approvals

<b>Approvals:</b>	Bureau Veritas DNV-GL Lloyds Register of Shipping UL + C-UL
<b>Certificates:</b>	Certificate of manufacturer according to RMRS Protection category
<b>Declarations:</b>	Declaration of conformity