



ICY BOX IB-2281 MSK

Backplane for 8x 2.5" HDD or SSD in 2x 5.25" bay

Key features

- 2x Mini SAS host connector
- Supports SATA III / SAS II 6 Gbit/s, HDD height up to 15 mm
- Robust industrial design, full aluminum / metal
- 8x anti-vibration HDD carrier with key lock
- Two fans (5x5 cm) with alarm for fan malfunction
- Windows, macOS compatible



Packing content

1x IB-2281 MSK, 2x Mini SAS cable, 4x keys, 1x screw set, 1x manual

For professional duty

HDDs in the 2.5" form factor are getting more and more popular as their storage capacity is growing. It is a logical consequence to employ them in servers. That's why ICY BOX offers a backplane that fits into a 2x 5.25" bay and holds 8x 2.5" SATA/SAS HDDs or SSDs. The height of the HDDs may even be 15 mm, for greatest storage capacity.

Technical data

Model	IB-2281 MSK
Article no.	60268
EAN code	4250078165941
Brand	ICY BOX
Colour	Black
Material	Aluminum + metal
HDD interface	8x SATA III / SAS II 6 Gbit/s
HDD height	5 - 15 mm
Required space	2x 5.25" bay
HDD capacity	Unlimited

Hot Swap	Yes
Host connection	2x Mini SAS connector
Transfer rate	Up to 6 Gbit/s
Operating system	Windows, macOS compatible
Lock	Yes
Fan	2x 5x5 cm fans
Operating temperatur	0°C ~ 55°C
Alarm	LED for fan failure
LED indicator	Power, HDD access, fan status
Power connector	2x 15 pin SATA power cable (not included)



ICY BOX IB-2281MSK

Backplane for 8x 2.5" HDD or SSD in 2x 5.25" bay



Eight times a week!

Eight 2.5" HDDs or SSDs fit into this enclosure and can be installed in 2x 5.25" bay in a PC, server or similar device. The enclosure is HotSwap capable, so the hard disks can be replaced without having to remove the enclosure.



Better safe than sorry

The enclosure is made entirely of metal and the trays are provided with a lock that prevents accidental opening and unauthorized access. An LED also indicates operation and disk access for each storage medium.



When it's hot

The aluminum dissipates heat very well and the cooling of the drives during heavy operation is ensured by two 50 mm fans on the back. An alarm warns of fan failure.

Logistical data

Packing unit:	8 pcs./carton
Total weight:	15,5 kg/carton
Gross weight: (with packing):	1.774 kg
Net weight:	1.522 kg

Dimension/carton:	520x380x280 mm
Dimension (with packing):	185x213x131 mm
Dimension of article:	163x145x85 mm
Country of origin:	China

