



M.2 22x42 22x60 22x80 22x110













# ICY BOX IB-2915MSCL-C31

# Docking & CloneStation for M.2 NVMe SSD and 2.5"/3.5" SATA SSD/HDD

### Key features

- Finally! Cloning from SATA to PCle NVMe (bidirectional)
- For M.2 SATA and 2.5"/3.5" drives
- For M.2 SSDs of sizes 22x 42/60/80 mm
- USB 3.2 Gen 2 high data transfer rates (up to 10 Gbit/s)
- LED for drive status and clone progress
- Quick, easy and toolless drive installation
- Cloning without computer (stand-alone)
- Use as HDD/SSD/NVMe DockingStation



### Packing content

1x IB-2915MSCL-C31, 1x Power supply, 1x USB cable, 3x M.2 rubber fixation, 1x Manual

Technical data

Model IB-2915MSCL-C31

Article no. 61017

**EAN** code 4250078173496

Colour Black Material Plastic

Interface to host computer USB 3.2 Gen 2 Type-C<sup>®</sup> / Type-A

**Transfer rate** Up to 10 Gbit/s M.2, 2.5", 3.5" **Drive size** 

**Drive height** Unlimited

**Drive interface** SATA I, II, III (6 Gbit/s) M.2 SATA, PCIe NVMe

 $M.2\ 22x\ 30/42/60/80\ mm$ 

**UASP** support Yes Plug & Play Yes ON/OFF button

LED Power, access and clone progress

Cooling

**Power supply** 12 V power adapter

**DC-Plug dimension**  $5.5 \times 2.1 \times 10$  mm (Ø outside x Ø inside x length) Operating system

Windows®, macOS®

One free USB 3.2 Gen 2 Type-C® or Type-A port System requirements

One M.2 PCle NVMe SSD 22x 30/42/60/80 mm

One M.2/2.5""/3.5"" SATA SSD/HDD








## ICY BOX IB-2915MSCL-C31

Docking & CloneStation for M.2 NVMe SSD and  $2.5^{\circ}$ / $3.5^{\circ}$  SATA SSD/HDD



# Simply clone everything

SATA to PCIe NVMe or PCIe NVMe to SATA, 2.5"/3.5" hard disks to M.2 or the other way round or M.2 to M.2: here, just anything goes with everything, and incredibly easily! The data media are installed and cloned completely without tools. The cloning direction is simply selected using a slide switch.



# Cloning made easy

Bit by bit and byte by byte without complicated software. The data carriers are simply inserted into the respective slot and cloned at the touch of a button. No matter whether from M.2/2.5"/3.5" SATA to M.2 NVMe or vice versa. Bidirectional and cross-technology cloning is now really easy.



## Flexible connection

Can also be used as external storage in DockingStation mode. With the included USB 3.2 Gen 2 combination cable, which is equipped with a USB Type-C® and the standard Type-A connection, the appropriate host connection can always be selected. The data races through the line at up to 10 Gbit/s.

Logistical data

Packing unit: 20 pcs. / carton Total weight: 9.340 kg Gross weight: (with packing): 0.429 kg Net weight:

Dimension (with packing): Dimension of article: Country of origin:

360x390x330 mm Dimension/carton: 65x145x170 mm 165x140x15 mm

