





ICY BOX IB-RD2253-C31

External RAID enclosure for 2x 2.5" SATA SSD

Key features

- Data availability external and compact
- Versatility RAID mode 1/0/JBOD (LARGE)/ SINGLE
- Performance advantage with USB 3.2 Gen 2 transfer rate of up to 10 Gbit/s
- High quality made of durable aluminium and robust plastic
- Compatibility Windows[®], macOS[®] or Chrome OS[™]



Packing content

1x IB-RD2253-C31, 1x USB Type-C° cable, 1x USB Type-A cable 1x Power adapter, 1x Screw set with screwdrivers, 1x Manual

Technical data

Model IB-RD2253-C31

Article no. 61028

 EAN code
 4250078173618

 Brand
 ICY BOX

 Colour
 Black

Material Aluminium, plastic

Interface to host computer USB 3.2 Gen 2 Type-C® / Type-A

Transfer rate Up to 10 Gbit/s

HDD size 2.5"

HDD height Up to 9.5 mm
HDD interface SATA I,II,III (6 Gbit/s)

HDD capacity Unlimited
UASP support Yes
Plug & Play Yes

RAID level 0, 1, LARGE, Single

LED Power, access and RAID mode

Cooling Passive

Power supply 5 V@2 A power adapter

 $\textbf{DC-Plug dimension} \hspace{0.5cm} 3.5 \times 1.35 \times 8 \hspace{0.1cm} \text{mm (\varnothing outside x \varnothing inside x length)}$

Operating system Windows®, macOS®, Chrome OS™

System requirements One free USB 3.2 Gen 2 Type-C® or Type-A port

One free 230 V EU power socket










ICY BOX **IB-RD2253-C31**External RAID enclosure for 2x 2.5" SATA SSD



Failure safety or performance

Double the security of your data by mirroring with RAID 1 or push the performance of your drives and data transfer rates to the limits with RAID 0. Use each installed drive separately with SINGLE mode or the entire available storage volume in LARGE mode.



Data transfer at top speed

With USB 3.2 Gen 2 you enjoy data transfer rates of up to 10 Gbit/s without waiting times or delay and can transport files from one drive to another within seconds. To suit your current equipment best, the IB-RD2253-C31 comes fully equipped with both a USB Type-C® and a Type-A cable.



Compact and resilient

The enclosure is made from aluminium and therefore very durable. Designed with passive cooling and without a fan, both professional and private workplaces benefit from this very silent setup. A status LED keeps you informed about the current state of the installed drives at all times.

Logistical data

 Packing unit:
 20 pcs. / carton

 Total weight:
 10.74 kg

 Gross weight (with packing):
 0.494 kg

 Net weight:
 0.187 kg

 Dimension/carton:
 506x341x270 mm

 Dimension (with packing):
 66x131x231 mm

 Dimension of article:
 130x84x26 mm

 Country of origin:
 China

RaidSonic Technology GmbH