



IB-865 3.5" Card Reader with USB 3.0 front interface

Key features

- Internal USB 3.0 interface for Superspeed 5 Gbit/s
- Fits into a standard 3.5" drive bay
- 6x card reader slot
- Supports more than 60 memory cards
- 1x USB 3.0 front interface
- · OS independent

Connection IB-865

Just connect the 20Pin USB 3.0 cable to the internal USB 3.0 connector on the mainboard, then you can read and write over 60 different kind of memory cards. The transfer rate is much faster than USB 2.0 connection. Additionally, a USB 3.0 front interface has been integrated for a better usability.

Technical data

 Model
 IB-865

 Article No.
 20065

 EAN code
 4250078185802

 Brand
 ICY BOX

Article text 3.5" Card Reader with USB 3.0 front interface

Colour Black
Material Metal/plastic
Required space 1x 3.5"

Memory card support Generic type of cards:

xD, SD, SDHC, SDXC, MMC, RS MMC, MicroSD, CFI, CFII, MD, MS, MS Pro, MS Pro Duo, M2

1x USB 3.0,

External data interface/ Front port

 $\stackrel{\cdot}{}$ 6x card reader slot Length of internal data cable 600 mm

Operating system OS independent
Transfer rate USB 3.0 up to 5 Gbit/s

Power switch N


LED Power and Access
Power connector Power via USB

RaidSonic Technology GmbH • Kurt-Fischer-Straße 50 • 22926 Ahrensburg / Germany Telefon: +49-(0)4102 -468 900 (Vertrieb) • Fax: +49-(0)4102 -468 901 • www.raidsonic.de Offers and deliveries are only done under our General Terms and Conditions. Errors and omissions excepted.





Front view



Rear view



- 1. Card reader slot (6x)
- 2. USB 3.0 Anschluss (1x)
- 3. LED Power
- 4. LED Access

1x USB 3.0 20Pin connection to 1x USB 3.0 20Pin host (Mainbord)

Packing content: 1x IB-865, 1x screw set, 1x manual

Logistical data

Packing unit: 10 pcs./carton Total weight: 4.5 kg/carton Gross weight: 0.392 kg Net weight: 0.264 kg

Dimension/Carton: 385x290x220 mm Dimension (with packing): Dimension of article:

197x73x140 mm 102x24.5x119 mm

Country of Origin: China

RaidSonic Technology GmbH • Kurt-Fischer-Straße 50 • 22926 Ahrensburg / Germany Telefon: +49-(0)4102 - 468 900 (Vertrieb) • Fax: +49-(0)4102 - 468 901 • www.raidsonic.de Offers and deliveries are only done under our General Terms and Conditions. Errors and omissions excepted.



Import tax: 84733080