

L-1

Design icon and productivity booster - Now with LED!











L-1 LED

L-1 LED





L-1 LED













L-1 LED Wall

L-1 LED Wall



automatically shut off after 4 or 9h in order to

save energy.

1 -1

Design icon and productivity booster - Now with LED!

Description

A prime example of how versatility, quality and stylish design can produce a product of such long-lasting popularity. L-1 is the world's original architect lamp designed in 1937 by Luxo's founder, Jac Jacobsen. Since its creation, 25 million L-1 luminaires have been sold worldwide, and L-1 has been distinguished by many prestigious awards in the world of industrial design. The unique design and flexible spring-balanced arm have earned L-1 a place among the world's all time classics.

L-1 LED

The classic L-1 is now available with a modern LED module. Light emitting diodes have an incredibly long life span. The diodes in L-1 LED have a life expectancy of 50,000 hours. L-1 LED is dimmable and has an automatic shut-off after 4 or 9 hours in order to save energy. That means 25 years or more with normal office use. You may never have to change the light source!

Standard with table clamp. Table base and integrated table mounts available on request. Colours: White, black or silver grey.

Wall version of L-1 LED!

The classic L-1 LED is now available as a wall version. A 20cm arm gives the classic task light a new, decorative use within the office segment.

Technical description


Body material & colour Optics	Steel arm and aluminium shade. Colours: white, black or aluminium grey. L-1 LED Wall is only available in white or black Symmetric light output. Inner shade painted white for maximum efficiency. L-1 LED has a	Mounting options	Standard with table clamp (A-clamp). Table base and integrated table mounts (TT table mount and TE bushing) are available on request.
	opalic diffuser for a softer light and to avoid glare.		L-1 LED Wall is delivered with standard wall bracket (WBR).
Power supply	Plug-in 20V power supply for LED version.		
Light source	Supplied with 1 x TC-HSE 11 W. L-1 is certified for maximum 11W CFL LED 700 lumen out Colour rendition index (CRI) is 90 Correlated colour temperature (CCT) is 3000 K	Arm technology and movement	Parallel, spring-balanced, three-pivot arm. Arm length is 100 cm. Up-and-down and rotational head movement. NB! Allowing for upward head tilt creates more flexibility but may cause unwanted glare.
			L-1 LED Wall has a 20cm short arm.
		Timer	L-1 LED has a timer. The light will

glamox.com/uk 22/03/2018 Page 2/4




L-1 Design icon and productivity booster - Now with LED!

Measurement drawings



L-1 (USA)




L-1 Wall


glamox.com/uk 22/03/2018 Page 3/4




L-1 Design icon and productivity booster - Now with LED!


Light measurement drawings





Energy label





glamox.com/uk 22/03/2018 Page 4/4