PRODUCT SPECIFICATION

Brand Kasp

Product Range Lock-off Hasps
Catalogue number 200,810,811
Date 21/12/2015



Range Description

Safety Lock-off hasps

Features

Kasp 200 Series

Health & Safety regulations demand that industrial plant and machinery power units are isolated whilst maintenance work is carried out. Kasp 200 series lock off hasps combined with Kasp 124 series brass padlocks offer an ideal solution, allowing up to 6 workers to lock off an individual energy source. 10 year guarantee.

- Heavy duty steel construction
- Zinc coated for corrosion protection
- Plastic coated for protecting painted surfaces



Easifit MCB Lockout - K81010

Universal Mini Circuit Breaker for single to triple switches. Simple and quick installation with no tools. Place over the switch, tighten with finger and thumb, rotate screw toggle and lockout with padlock as normal.



Essential Lockout Kit - K81100

A unique kit with all the essential parts needed to lock off one mini circuit breaker.

The kit includes:- Easifit MCB Lockout, Brass Padlock 25mm, Danger/Identitiy Tag and a handy carabiner to hold the kit together.



Item Number	Item Description	EAN No	Commodity	Carton
	•		code	Qty
K20025	Lock off hasp 25mm	5013969902914	8301500	6
K20038	Lock off hasp 38mm	5013969025729	8301500	6
K81010	Easifit MCB Lockout	5013969904512	8301500000	220
K81100	Essential Lockout Kit	5013969904529	8301500000	24

Technical product	
information	
Standards	Non applicable
compliance	
User health and	None applicable
safety information	
RoHS/WEEE	This product range does not fall within the scope of WEEE or RoHS
compliance	regulations
Material safety	None applicable
data	
Warranty	Kasp products are guaranteed against defects in manufacture and/or
	materials for 10 years
	Damage caused through inappropriate use or attempted break in is not
	covered
Country of origin	K200 series Taiwan
	K81010 & K81100 China

Dimensional details

	Product only				Product on primary packaging			
Item	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
K20025	45	10	130	114				
K20038	60	10	140	122				
K81010	40	18	40	24	80	30	155	37
K81100	-	-	-	-	145	20	200	108

	Shelf box	x (secondary	Euro Pallet data Wi x Hi			
Item	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
K20025	50	140	58	730		
K20038	65	155	55	790		
K81010	190	235	210	10160		
K81100	398	435	425	2760		

Packaging waste details

	Primary Packaging				Secondary packaging			
Item	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
K20025	1	Bag					28	Box
K20038	1	Bag					34	Box
K81010	12	Blister	2	Backing Card			202	Box
K81100	1	Shrink Wrap	10	Backing Card			160	Box