

Crimp Assortments

for end sleeves (ferrules)

97

- > In a TANOS MINI-systainer® (solid plastic box)
- > T-Loc fastener for one-handed operation: open or close the systainer® with one turn and connect to a second systainer®
- > Opening when connected: fast and simple access to content without disconnecting
- > Two stackable plastic inserts with 6 trays each for connectors
- > With an assortment of end sleeves (ferrules) with/without collar).



97 90 05

- > With Crimping Pliers for end sleeves
97 71 180

97 90 06

- > With Crimping Pliers for end sleeves
97 71 180

97 90 09

- > With Self-Adjusting Crimping Pliers for End Sleeves (ferrules) 97 53 04

97 90 10

- > With Self-Adjusting Insulation Stripper 12 40 200 ; with Self-Adjusting Crimping Pliers for End Sleeves (ferrules)
97 53 04



97 90 05



97 90 06



97 90 09



97 90 10



97 90 12



97 90 23



97 90 24



Several boxes can be connected with each other

Article No.	EAN 4003773-	Pliers		200 x mm ²	150 x mm ²	100 x mm ²	75 x mm ²	50 x mm ²	40 x mm ²
97 90 05	025535	97 71 180		0.5 / 0.75 / 1 / 1.5 / 2.5	4 / 6			10 / 16	
97 90 06	025542	97 71 180		0.5 / 0.75 / 1 / 1.5	2.5		4 / 6	10	16
97 90 09	028574	97 53 04		0.5 / 0.75 / 1 / 1.5 / 2.5		4 / 6		10	
97 90 10	046202	97 53 04 / 12 40 200		0.5 / 0.75 / 1 / 1.5 / 2.5		4 / 6		10	
97 90 12	048916	97 53 08 / 12 40 200		0.5 / 0.75 / 1 / 1.5 / 2.5		4 / 6		10	
97 90 23	062158	97 52 38		0.5 / 0.75 / 1 / 1.5 / 2.5		4 / 6			
97 90 24	062394	97 53 08 / 12 42 195		0.5 / 0.75 / 1 / 1.5 / 2.5		4 / 6		10	
97 90 00 LE	054009	TANOS MINI-systainer® empty							

97 90 00

> With crimping pliers 97 00 215 A

97 90 21

> With Crimping Pliers PreciForce®
97 52 36 (for insulated terminals
and plug connectors)

97 90 22

> With Self-Adapting Universal
Insulation Stripper "Multistrip 10"
12 42 195

> With Crimping Pliers PreciForce®
97 52 36 (for insulated terminals
and plug connectors)

97 90 25

> With crimping pliers 97 22 240

97 90 26

> With crimping pliers 97 32 240



Article No.	EAN 4003773-		Cable connectors	Quantity	Cable mm²
97 90 00	025375		Blade Terminal Sockets, 6.3 x 0.8 mm Round Sockets, Ø 4 mm Cable Connectors, eye type, Ø 4 mm Cable Connectors, eye type, Ø 5 mm Cable Connectors, eye type, Ø 6 mm Butt Connectors, insulated, Red Butt Connectors, insulated, Blue Round Pin Plugs, Ø 4 mm	25 25 25 25 25 25 25 25	4 – 6 1.5 – 2.5 0.5 – 1 0.5 – 1 1.5 – 2.5 0.5 – 1 1.5 – 2.5 0.5 – 1
97 90 21	062134		Blade Terminal Sockets, 6.3 x 0.8 mm Cable Connectors, eye type, Ø 4 mm Cable Connectors, eye type, Ø 5 mm Cable Connectors, eye type, Ø 6 mm Cable Connectors, eye type, Ø 8 mm Cable Connectors, eye type, Ø 4 mm Cable Connectors, eye type, Ø 5 mm Cable Connectors, eye type, Ø 6 mm Butt Connectors, insulated, Red Butt Connectors, insulated, Yellow Butt Connectors, insulated, Blue	25 25 25 25 25 25 25 25 25 25 25	0.5 – 1 1.5 – 2.5 0.5 – 1 0.5 – 1 4 – 6 1.5 – 2.5 1.5 – 2.5 1.5 – 2.5 0.5 – 1 4 – 6 1.5 – 2.5
97 90 22	062141		Blade Terminal Sockets, 6.3 x 0.8 mm Cable Connectors, eye type, Ø 4 mm Cable Connectors, eye type, Ø 5 mm Cable Connectors, eye type, Ø 4 mm Cable Connectors, eye type, Ø 5 mm Cable Connectors, eye type, Ø 6 mm Cable Connectors, eye type, Ø 8 mm Butt Connectors, insulated, Red Butt Connectors, insulated, Blue Butt Connectors, insulated, Yellow	25 25 25 25 25 25 25 25 25 25	0.5 – 1 1.5 – 2.5 0.5 – 1 0.5 – 1 1.5 – 2.5 1.5 – 2.5 4 – 6 4 – 6 0.5 – 1 1.5 – 2.5 4 – 6