

## LUMILUX COMBI LED-E

Expansion luminaires for continuous row arrangement



### Areas of application

- Offices, hotels, living areas
- Corridors, entrances, foyers, stairwells, elevators
- Counters, reception and waiting areas, wardrobes, mirrors
- Shops, changing rooms, shop windows
- Cove lighting, even in tight spaces
- Shelves, furniture integration or under cabinet mounting
- Kitchens, workspaces
- Continuous row luminaire as architectural design element

### Product benefits

- Extension luminaire to LUMILUX Combi LED -F and -N
- For continuous rows without dark spots of up to 13 luminaires (up to 15 m)
- Easy and quick series connection thanks to simple plug system

### Product features

- Integrated ECG
- High-quality appearance thanks to anodized aluminum housing and matt diffuser
- No visible differences in light color between luminaires thanks to fine binning
- High luminous efficacy: up to 100 lm/W



## Product family datasheet

### Technical data

Product description	Electrical data			Photometrical data				Light technical data	Dimensions & weight	
	Nominal wattage	Nominal voltage	Mains frequency	Color temperature	Luminous flux	Light color (designation)	Color rendering index Ra	Light distribution	Length	Width
LUMILUX COMBI LED -E 18 W 3000 K	18 W	220...240 V	50/60 Hz	3000 K	1800 lm	Warm white	>80	Symmetric	1180 mm	25.0 mm
LUMILUX COMBI LED -E 18 W 4000 K	18 W	220...240 V	50/60 Hz	4000 K	1850 lm	Cool white	>80	Symmetric	1180 mm	25.0 mm

Product description	Height	Colors & materials			Temperatures & operating conditions	Capabilities		Certificates & standards
		Body material	Product color	Cover material	Ambient temperature range	Type of installation	Type of connection	Protection class
LUMILUX COMBI LED -E 18 W 3000 K	44.0 mm	Aluminum	Silver	Polycarbonate (PC)	-20...+40 °C	Surface-mounted	System connector: socket	II
LUMILUX COMBI LED -E 18 W 4000 K	44.0 mm	Aluminum	Silver	Polycarbonate (PC)	-20...+40 °C	Surface-mounted	System connector: socket	II

Product description	Type of protection	Country specific categorizations
		Order reference
LUMILUX COMBI LED -E 18 W 3000 K	IP20	72827
LUMILUX COMBI LED -E 18 W 4000 K	IP20	72828

### Equipment / Accessories

- Fixed connector and flexible connecting cable included
- Complete mounting and connecting accessories included

### Application advice

## Product family datasheet

For more detailed application information and graphics please see product datasheet.

---

### Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4052899932791	LUMILUX COMBI LED -E 18 W 3000 K	Shipping carton box 2	1430 mm x 77 mm x 60 mm	6.61 dm <sup>3</sup>	1940.00 g
4052899932876	LUMILUX COMBI LED -E 18 W 4000 K	Shipping carton box 2	1430 mm x 77 mm x 60 mm	6.61 dm <sup>3</sup>	1800.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

---

### Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.