



KCUABbk



KCUAA2



KCUAAXbk



KCUAA3bk2




KCUAA311wh




KCHDbk



KCK66



KOCMM



KOCSM



KOLMMDX



KOLSMDX



KOTSM



KOTMM



SKmc



FACK2



SACK2



FACK2S



SACK3S



SGKSsu+



SGACK2S




SACK90



SEKei



KBNC50



KBNC75







KSP



SKF\*



KSH66



KCF



KGB-1



KPK



KRCA\*bk/KRCA\*wh



KC3.5



SLJ



Code	Description	Colour
KCUABbk	USB A female to B female adaptor, reversible	●
KCUAA2*	USB2.0 A female to A female coupler	●○
KCUAAXbk	USB2.0 A female to A female coupler, reversible	●
KCUAA3bk2	USB3 female to female coupler, cross-wired	●
KCUAA311wh	USB3 female to female coupler, wired 1:1	○
KCHDbk	HDMI female to female coupler	●
KCK66	RJ12 6P6C female to female coupler	●
KOCMM	Fibre female to female coupler SC to SC, multi mode simplex	○●
KOCSM	Fibre female to female coupler SC to SC, single mode simplex	○●
KOLMMDX	Fibre female to female coupler LC to LC, multi mode duplex	○●
KOLSMDX	Fibre female to female coupler LC to LC, single mode duplex	○●
KOTSM	Fibre female to female coupler ST to ST, single mode simplex, yellow dustcover	○●
KOTMM	Fibre female to female coupler ST to ST, multi mode simplex, black dustcover	○●
SKmc*	Category 6 IDC socket, LSA-Plus and 110 type termination, unshielded	○●
FAK2*	Category 5e female to female coupler, unshielded	○●
SACK2*	Category 6 female to female coupler, unshielded	○●
FAK2S	Category 5e female to female coupler, shielded	●
SACK3S	Category 6 female to female coupler, shielded	●
SGKSsu+	Category 6A tool-less socket, shielded	●
SGACK2S	Category 6A female to female coupler, shielded (Cat 6 coupler, shielded also available)	●
SACK90*	Cat 6 female to female coupler, w/rear outlet 90° to front outlet, shielded or unshielded	○●○
SEKei	Category 8 tool-less socket, shielded	●
KBNC50*	BNC 50 ohm female to female coupler	○●
KBNC75*	BNC true 75 ohm female to female coupler(capable of data rates up to 3 Gb/s or higher)	○●
KSP*	Speaker module in black with elastic identifier (coloured, red or black)	●●
SKF*/SKFS	Category 6 tool-less IDC socket (Category 5e also available)	○●●●●●
KSH66	RJ12 6p6c socket	●
KCF*	F connector, female to female coupler in black.	○●

KGB-1*	UK telephone socket - PSTN Master (Slave/Secondary version also available)	○●
KPK*	Clip-in blank	○●
KRCA*wh/KRCA*bk	RCA coupler - available with black/white/yellow/red insert	○●
KC3.5*	3.5mm coupler	○●
SLJ*	LOKJAC Category 6 tool-less locking keystone	○●

\* Shielded = S , Black = bk , White = wh , Blue = bl , Orange = or , Red = rd , Green = gn , Yellow = yw

## Specifications:

- For detailed specifications see separate web pages as follows:

USB A female to B female coupler: [http://www.tuk.co.uk/tuk\\_live/product\\_details.php?category\\_id=&pld=182](http://www.tuk.co.uk/tuk_live/product_details.php?category_id=&pld=182)

USB2.0 A female to A female: [http://www.tuk.co.uk/tuk\\_live/product\\_details.php?category\\_id=&pld=224](http://www.tuk.co.uk/tuk_live/product_details.php?category_id=&pld=224)

USB2.0 A female to A female, reversible: [http://www.tuk.co.uk/tuk\\_live/product\\_details.php?category\\_id=&pld=279](http://www.tuk.co.uk/tuk_live/product_details.php?category_id=&pld=279)

USB3 female to female coupler, cross-wired: [http://www.tuk.co.uk/tuk\\_live/product\\_details.php?category\\_id=1&pld=267](http://www.tuk.co.uk/tuk_live/product_details.php?category_id=1&pld=267)

USB3 female to female coupler, wired 1:1: [http://www.tuk.co.uk/tuk\\_live/product\\_details.php?category\\_id=1&pld=269](http://www.tuk.co.uk/tuk_live/product_details.php?category_id=1&pld=269)

HDMI female to female coupler: [http://www.tuk.co.uk/tuk\\_live/product\\_details.php?category\\_id=&pld=185](http://www.tuk.co.uk/tuk_live/product_details.php?category_id=&pld=185)

RJ12 female to female coupler: [http://www.tuk.co.uk/tuk\\_live/product\\_details.php?category\\_id=&pld=170](http://www.tuk.co.uk/tuk_live/product_details.php?category_id=&pld=170)

Fibre female to female couplers: [http://www.tuk.co.uk/tuk\\_live/product\\_details.php?category\\_id=&pld=209](http://www.tuk.co.uk/tuk_live/product_details.php?category_id=&pld=209)

Cat 6 IDC UTP jack: [http://www.tuk.co.uk/tuk\\_live/product\\_details.php?category\\_id=&pld=192](http://www.tuk.co.uk/tuk_live/product_details.php?category_id=&pld=192)

Cat 5e UTP and FTP female to female coupler: [http://www.tuk.co.uk/tuk\\_live/product\\_details.php?category\\_id=&pld=246](http://www.tuk.co.uk/tuk_live/product_details.php?category_id=&pld=246)

Cat 6 UTP and FTP female to female coupler: [http://www.tuk.co.uk/tuk\\_live/product\\_details.php?category\\_id=&pld=243](http://www.tuk.co.uk/tuk_live/product_details.php?category_id=&pld=243)

Cat 6A FTP jack: [http://www.tuk.co.uk/tuk\\_live/product\\_details.php?category\\_id=&pld=113](http://www.tuk.co.uk/tuk_live/product_details.php?category_id=&pld=113)

Cat 6A FTP female to female coupler: [http://www.tuk.co.uk/tuk\\_live/product\\_details.php?category\\_id=&pld=150](http://www.tuk.co.uk/tuk_live/product_details.php?category_id=&pld=150)

90° Cat 6 panel mount female to female coupler: [http://www.tuk.co.uk/tuk\\_live/product\\_details.php?category\\_id=&pld=133](http://www.tuk.co.uk/tuk_live/product_details.php?category_id=&pld=133)

Cat 8 FTP socket: [http://www.tuk.co.uk/tuk\\_live/product\\_details.php?category\\_id=1&pld=345](http://www.tuk.co.uk/tuk_live/product_details.php?category_id=1&pld=345)

BNC 50 ohm female to female coupler: [http://www.tuk.co.uk/tuk\\_live/product\\_details.php?category\\_id=&pld=218](http://www.tuk.co.uk/tuk_live/product_details.php?category_id=&pld=218)

BNC true 75 ohm female to female coupler: [http://www.tuk.co.uk/tuk\\_live/product\\_details.php?category\\_id=&pld=221](http://www.tuk.co.uk/tuk_live/product_details.php?category_id=&pld=221)

Speaker module: [http://www.tuk.co.uk/tuk\\_live/product\\_details.php?category\\_id=&pld=201](http://www.tuk.co.uk/tuk_live/product_details.php?category_id=&pld=201)

Cat 5e and Cat6 tool-less UTP socket: [http://www.tuk.co.uk/tuk\\_live/product\\_details.php?category\\_id=&pld=173](http://www.tuk.co.uk/tuk_live/product_details.php?category_id=&pld=173)

Cat 6/6A tool-less STP keystone socket SKFS:  
[http://www.tuk.co.uk/tuk\\_live/product\\_details.php?category\\_id=&pld=299](http://www.tuk.co.uk/tuk_live/product_details.php?category_id=&pld=299)

RJ12 6p6c socket: [http://www.tuk.co.uk/tuk\\_live/product\\_details.php?category\\_id=&pld=264](http://www.tuk.co.uk/tuk_live/product_details.php?category_id=&pld=264)

F connector female to female coupler: [http://www.tuk.co.uk/tuk\\_live/product\\_details.php?category\\_id=&pld=255](http://www.tuk.co.uk/tuk_live/product_details.php?category_id=&pld=255)

UK telephone socket: [http://www.tuk.co.uk/tuk\\_live/product\\_details.php?category\\_id=&pld=280](http://www.tuk.co.uk/tuk_live/product_details.php?category_id=&pld=280)

RCA coupler: [http://www.tuk.co.uk/tuk\\_live/product\\_details.php?category\\_id=1&pld=296](http://www.tuk.co.uk/tuk_live/product_details.php?category_id=1&pld=296)

3.5mm coupler: [http://www.tuk.co.uk/tuk\\_live/product\\_details.php?category\\_id=1&pld=309](http://www.tuk.co.uk/tuk_live/product_details.php?category_id=1&pld=309)


LOKJAC Category 6 tool-less locking keystone: [http://www.tuk.co.uk/tuk\\_live/product\\_details.php?category\\_id=1&pld=302](http://www.tuk.co.uk/tuk_live/product_details.php?category_id=1&pld=302)

- Our keystones are designed for a standard cut-out measuring 14.86mm wide x 19.4mm high in a panel approximately 1.3mm thick. For aesthetic reasons, we recommend a twin walled panel, or an adaptor, like our KApma.

2nd October, 2018

TUK Ltd, Unit 4, Wimbledon Stadium Business Centre, Riverside Road, London SW17 0BA

Tel: +44 (0) 20 8946 6688 Fax: +44 (0) 20 8879 7410 Email: [sales@tuk.co.uk](mailto:sales@tuk.co.uk) Website: [www.tuk.co.uk](http://www.tuk.co.uk)

TUK follows a policy of continuous improvement. All information is correct at the time of printing but may be subject to change without prior notification. Please contact TUK for formal confirmation of current specification. HDMI and LSA-Plus are registered trademarks of HDMI Licensing and Krone (UK) Technique Ltd respectively, whose rights are acknowledged.  is a registered trademark of TUK Limited.