














logitech®

IDEAL PRODUCTS
FOR EVERY
BUSINESS



	CORDED COMBO	WIRELESS COMBOS					CORDED KEYBOARDS		WIRELESS KEYBOARDS				
													
	MK120	MK270	MK520	MK710	MK850	MX800	K120 for Business	K740	Craft	K750	K400 Professional	K480	K780
Reference (UK)	920-002552	920-004523	920-002606	920-002429	920-008224	920-006243	920-002501	920-005694	920-008503	920-002929	920-008362	920-006364 Black 920-006365 White	920-008041
EAN Code (UK)	5099206020603	5099206039292	5099206022638	5099206021037	5099206066854	5099206051430	5099206020849	5099206045972	5099206072879	5099206025707	5099206070622	5099206052802 5099206052819	5099206065017
Connectivity	USB	USB Nano-receiver	USB Unifying	USB Unifying	USB Unifying Bluetooth Smart	USB Unifying	USB	USB	USB Unifying Bluetooth® Smart	USB Unifying	USB Unifying	Bluetooth 3.0	USB Unifying Bluetooth® Smart
Flow enabled	NO	NO	NO	NO	YES	NO	NO	NO	YES	NO	NO	NO	YES
Battery Life	Corded	24 months (KB) 12 months (M)	36 months (KB) 12 months (M)	36 months	36 months (KB) 24 months (M)	Rechargeable 10 days (KB) 1 month (M)	Corded	Corded	Rechargeable, 1 week	Solar, up to 3 months in total darkness	18 months	24 months	24 months
Media Hot Keys	NO	8 Separate Hot Keys	6 Separate Hot Keys	6 Separate Hot Keys + LCD Screen	15 integrated media and shortcut hot keys	12 Function-Integrated Hot Keys	-	12 Function-Integrated Hot Keys	12 Function-Integrated shortcuts and 5 separate hot keys (17)	12 Function-Integrated Hot Keys	13 Function-Integrated Hot Keys	12 integrated media and shortcut hot keys	9 Function-Integrated Hot Keys
Illuminated Caps Lock	YES	YES	NO	YES	YES	YES (on key)	YES	YES	YES	NO	NO	NO	NO
Spill Resistant	YES	YES	YES	YES	YES	NO	YES	NO	NO	NO	YES	YES	NO
Cable/Wireless Length	Cable 1.5 m (KB)/1.8 m (M)	10 m (2.4 GHz)	10 m (2.4 GHz)	10 m (2.4 GHz)	10 m (2.4 GHz)	10 m (2.4 GHz)	Cable 1.5 m	Cable 1.8 m	10 m (2.4GHz)	10 m (2.4 GHz)	10 m (2.4 GHz)	11 m (2.4 GHz)	10 m (2.4 GHz)
Warranty	3 years	3 years	3 years	3 years	2 years	3 years	3 years	3 years	2 years	3 years	2 years	2 years	2 years

	For iPad 5th Generation	For iPad Pro 10.5"	For iPad Pro 12.9"	For iPad Pro 9.7" and 12.9"	For 9 - 10" tablets
	Slim Folio	Slim Combo	Slim Combo	Base	Universal Folio
					
Reference (UK)	920-008624	920-008448	920-008440	939-001471	920-008341
EAN Code (UK)	5099206073876	5099206071407	5099206071339	5099206067011	5099206069749
Description	Case with integrated Bluetooth keyboard for iPad	Versatile case with detachable keyboard and Smart Connector	Versatile case with detachable keyboard and Smart Connector	Charging stand with Smart Connector	Universal folio with integrated Bluetooth keyboard
Battery Life	4 years	-	-	-	2 years
Closing Mechanism	Magnet	Magnet	Magnet	-	Elastic band
Connection Type	Bluetooth®	Smart Connector	Smart Connector	Smart Connector	Bluetooth®
Warranty	3 years	2 years	2 years	2 years	2 years











	UC products			
	ConferenceCam Connect	MeetUp	Group	PTZ Pro 2 Camera
Reference	960-001014	960-001102	960-001057	960-001186
EAN Code	5099206055971	5099206072060	5099206062528	5099206070455
Certification	Skype for Business, Cisco, Skype, work with most UC platforms	Skype for Business, Cisco, Skype, work with most UC platform	Skype for Business, Cisco, Skype, work with most UC platforms	Skype for Business, Cisco, Skype, work with most UC platforms
Short Description	HD video and 360-degree sound optimized for Huddle Rooms Portable and rechargeable device	ConferenceCam designed for huddle rooms	Video conferencing for mid to large-sized meeting rooms	Premium USB-enabled HD PTZ video camera for use in conference rooms, large events and other professional video uses
Room Size	3.7m/12' diameter - Up to 6 participants	Huddleroom optimized up to 6 participants. With optional expansion mic up to 8 participants.	Mid to large size room optimized up to 14 participants. With optional expansion mics up to 20 participants.	Mid to large rooms, including conference rooms and auditoriums, with existing audio capabilities
Microphone	2 omni-directional mics	3 omni-directional mics	4 omni-directional mics	-
Pan, Tilt, Zoom	Digital Pan and Tilt to 4X zoom (HD)	Motorized pan & tilt Expand field of view up to 170°. 5x HD zoom Zero	260° pan/130° tilt with 10x loseless zoom	260° pan/130° tilt with 10x loseless zoom
Video Resolution	Full HD 1080p 30fps	4k Ultra Hd - Full HD 1080p 30fps	Full HD 1080p 30fps	HD 1080p @ 30fps
Field of View (FOV)	90° diagonal	Super-wide 120° field of view	90° diagonal	90° diagonal
Warranty	2 years	2 years	2 years	2 years

	Presenters		
	R400	R700	Spotlight Plus

Reference	910-001356	910-003506	910-005166
EAN Code	5099206018112	5099206040861	5099206072138
Tracking	-	-	-
Connectivity	USB 2.4 GHz	USB 2.4 GHz	USB 2.4 GHz Bluetooth®
Battery Life	-	-	Rechargeable, 3 months
Scrolling	-	-	-
Number of Buttons	-	-	3 (customizable)
Cable/Wireless Length	15 m (2.4 GHz)	30 m (2.4 GHz)	30 m (2.4 GHz)
Warranty	3 years	3 years	3 years

	Corded Mice		Pointing devices wireless								Pointing devices silent	
	B100	M500	B170	M325	M525	M560	M705	M720	MX Anywhere 2S	MX Master 2S	B330 Silent Plus	M590
Reference	910-003357 Black 910-003360 White	910-003726	910-004798	910-002142 Dark Grey 910-002334 Grey	910-004932 Black 910-004933 Blue	910-003882 Black 910-003913 White	910-001949	910-004791	910-005153	910-005139	910-004913	910-005197
EAN Code	5099206041271 Black 5099206041288 White	5099206048324	5099206065062	5099206026094 5099206027770	5099206067783 5099206067790	5099206047310	5099206023901	5099206065086	5099206073050	5099206073029	5099206066717	5099206072558
Tracking	Optical	Laser	Optical (1000 DPI)	Laser Grade (1000 DPI)	Laser Grade (1000 DPI)	Laser Grade (1000 DPI)	Laser Grade (1000 DPI)	Optical	Darkfield (up to 4000 DPI)	Darkfield (up to 4000 DPI)	Laser Grade (1000 DPI)	Laser Grade (1000 DPI)
Connectivity	USB	USB	USB Nano-Receiver	USB Unifying	USB Unifying	USB Unifying	USB Unifying	USB Unifying Bluetooth® Smart	USB Unifying Bluetooth® Smart	USB Unifying Bluetooth® Smart	USB Nano-receiver (Unifying ready)	USB Unifying Bluetooth®
Flow enabled	NO	NO	NO	NO	NO	NO	NO	YES	YES	YES	NO	YES
Battery Life	Corded	Corded	12 months	18 months	36 months	18 months	36 months	24 months	Rechargeable, up to 70 days	Rechargeable, up to 70 days	24 months	24 months
Scrolling	Ratchet Wheel	Hyperfast	Ratchet Wheel	Micro-Precise Wheel	Micro-Precise Wheel	Hyperfast	Hyperfast	Hyperfast	Hyperfast	Hyperfast + Thumb wheel	Micro-Precise Wheel (Quiet)	Micro-Precise Wheel
Number of Buttons	3	7	3	5	5	7	8	8	7	9	5	5
Cable/Wireless Length	1.8 m	1.8 m	10 m (2.4 GHz)	10 m (2.4 GHz)	10 m (2.4 GHz)	10 m (2.4 GHz)	10 m (2.4 GHz)	10 m (2.4 GHz)	10 m (2.4 GHz)	10 m (2.4 GHz)	10 m (2.4 GHz)	10 m (2.4 GHz)
Warranty	3 years	3 years	2 years	3 years	3 years	3 years	3 years	2 years	2 years	2 years	2 years	2 years

Headsets				
	H570e Stereo	H650e Stereo	H820e Mono	PC 960
				
Reference	981-000575	981-000519	981-000512	981-000100
EAN Code	5099206053304	5099206041196	5099206041622	5099206008441
Stereo	YES	YES	NO	YES
Rotating Microphone	YES	YES	YES	YES
Monoversion available	YES	YES	YES	NO
Certified by	Lync Skype Cisco	Lync Skype Cisco	Lync Skype Cisco	-
Connection	USB	USB	DECT spectrum (Wireless) USB	USB
Cable/Wireless Length	Cable 2.1 m	Cable 2.2 m	100 m	Cable 2.4 m
Audio Controls	YES	YES	YES	YES
Warranty	2 years	2 years	2 years	3 years

Webcams				
	B525	C925e	C930e	Brio
				
Reference	960-000842	960-001076	960-000972	960-001106
EAN Code	5099206030725	5099206064027	5099206045200	5099206068100
Video Resolution	HD 720	Full HD 1080	Full HD 1080	4k @30fps
Photo Resolution	2 MP	10 MP	10 MP	13 MP
Optics	-	-	Carl Zeiss	-
Certified by	Lync	Lync Skype Cisco	Lync Skype Cisco	Skype for Business
RightLight	YES	YES	YES	RightLight™ 3 with HDR
RightSound	YES	YES	YES	YES
Warranty	2 years	2 years	3 years	3 years

Logitech business website: business.logitech.com/ Logitech partner exchange website: partner.logitech.com

WHY CHOOSE LOGITECH MICE & KEYBOARDS

1. SIMPLE PLUG AND PLAY WITH UNIFYING™ TECHNOLOGY

The Logitech® Unifying™ receiver is a tiny, leave-in wireless USB device that controls mice and keyboards. The tiny Logitech® Unifying™ receiver is small enough to stay in a computer's USB port and doesn't stick out or fall off when a computer is transported. Its unique wireless protocol allows you to connect up to 6 compatible devices to the same single receiver, for example two sets of keyboards and mice, used at two different working locations.

2. DARKFIELD™ LASER TRACKING

Both optical and traditional laser mice use irregularities on the surface to track the direction and speed of the mouse movements. For this reason, traditional mice do not perform well on shiny surfaces. This is where Darkfield Laser Tracking comes in. Darkfield uses the smallest possible detail to create a microroadmap of the surface so you get a better precision on virtually any surface, even glass¹.

3. HYPERFAST SCROLL WHEEL

Logitech's hyper-fast scrolling lets you fly through long documents and Web pages with a single spin of a nearly frictionless metal scroll wheel. On the MX Master and the MX Anywhere 2 wireless mouse, you can experience a SPEED-ADAPTIVE SCROLL WHEEL. With the speed-adaptive scroll wheel you can scroll through long documents or web pages faster and easier. Press on the wheel and shift to click-to-click mode for precise navigation. In free-spinning mode, you coast smoothly and quickly through the longest documents and Web pages, stopping instantly when you need to.

4. MORE ABOUT EASY SWITCH TECHNOLOGY

Our world is increasingly a multi-screen and multi-workspace one in which ease and flexibility are key. Since it's common to use multiple devices at once, Logitech is helping to streamline your experience with the launch of the Easy-Switch technology. Connect our Easy-Switch keyboards and mice to 3 devices, and switch between them at the touch of a button.

5. ADVANCED 2.4 GHZ WIRELESS TECHNOLOGY

Our proprietary wireless technology offers:

- Fast data transmission, without delays or dropouts
- Range of up to 10 meters
- 128-bit AES encryption between keyboard and receiver.

With Logitech Advanced 2.4 GHz, your employees can get all the benefits of a corded device with the convenience of wireless. The typical latency of an Advanced 2.4 GHz device operating in a clean environment is below 10 ms².

6. ADVANCED ENCRYPTION STANDARD

The advanced encryption standard is a commonly used standard in software and hardware to encrypt sensitive data. Logitech wireless keyboards benefit from this encryption standard to protect the data transmitted between the keyboard and the plug-and-play USB receiver. Since the range of a wireless device may reach several tens of meters in an open environment, this encryption protects sensitive data such as passwords, customer information, or personal messages.

¹ 1.4 mm minimum thickness

² In a noisy environment, this latency may increase depending on the strength, type and occurrence of the interference.