



DELL MICRO
AIO STAND

MFS22

Maximize your desk space with the sleek all-in-one stand for your Optiplex Micro desktop and Dell monitor.



MFS22



Effortless Setup

Securely install your OptiPlex micro desktop with VESA-supported mounting. Attach the monitor effortlessly with Dell Quick Release.



Clutter-Free Workstation

For a clean desk experience, the sleek stand offers a cable routing system for tidy wiring and houses your monitor in a small footprint. The stylish cover keeps cables hidden from view.



Optimized for productivity and security

Fully adjustable for convenient, flexible viewing options, adjust height, tilt, swivel, and pivot your monitor to suit your viewing comfort. Securely house your micro desktop as the stand comes with support for both the Kensington lock and a padlock.



MFS22

Clutter-free design for a more comfortable workspace

Work comfortably with the adjustable Dell Micro AIO Stand (MFS22) with features that help enhance your productivity.

Tilt, pivot, and swivel easily to your **preferred viewing angle**.



Retractable swivel handle for easy transportation and setup.

Cable cover to hide cables from view.



Support for padlock and Kensington lock.

Cable management system for a cleaner desk.



Front routing loops for wrapping the excess cable length.

Pass-through hole on stand to route external cables to micro desktop/monitor.




Ability to **adjust the height** up to 150mm offers the flexibility in raising the monitor to a comfortable viewing level.

Dell Quick Release and VESA-supported mounting for **easy installation**.

The stands are **compatible with a wide range of monitor sizes** supporting 19" to 27" C / E / P / U Monitors.

3-Year Warranty¹



DELL MICRO AIO STAND

MFS22

FEATURE TECHNICAL SPECIFICATION

MODEL	Dell Micro AIO Stand – MFS22
COLOR	Silver
PANEL MOUNT	Supports Dell Quick Release Monitor; Adapter provided for use with VESA (100mm x 100mm) compliant monitors.
MONITOR SUPPORTABILITY	Selected 19" to 27" UltraSharp, P, E and C series monitors. E series monitors require the use of VESA Adapter.
MONITOR WEIGHT RANGE	4.8 – 12.8 lbs. (2.2kg ~ 5.8kg)
MONITOR ROTATION	Portrait to Landscape
MONITOR TILT RANGE	-5° to +21°
MONITOR SWIVEL RANGE	+/- 45° (via Riser interface to Stand Base)
PIVOT	Bi-directional (clockwise & anti-clockwise), no detent
HEIGHT ADJUSTMENT	5.90" (15cm)
CHASSIS	Platform Chassis with VESA (100mm x 100mm) Screw Holes design.
COMPATIBLE WITH OPTIPLEX MICRO PLATFORMS	OptiPlex MFF 7000 OptiPlex MFF 5000 OptiPlex MFF 3000 OptiPlex Thin Client 3000
CABLE MANAGEMENT	<ul style="list-style-type: none">· Cable routing hole on bottom side of Cable Cover.· Cable Routing Clips on the front of Stand Interposer to dress excess cable length.· Pass-through hole on stand to route external cables to MFF/Monitor.
SECURITY SLOT	K-Lock & Pad-Lock
WARRANTY	3 years Limited Hardware Warranty ¹
PACKAGE CONTENTS	Dell Micro AIO Stand, Cable Cover, VESA Step Screws, VESA® Adapter plate, thumbscrew, screws, spacers, documentation

¹ Limited Hardware Warranty: For copy of Ltd Hardware Warranty, write Dell USA LP, Attn: Warranties, One Dell Way, Round Rock, TX 78682 or see www.dell.com/warranty.

Product availability varies by country. Contact your Dell representative or visit Dell.com to learn more.

© 2022 Dell Inc. or its subsidiaries. All rights reserved. Dell Technologies, Dell, EMC, Dell EMC and other trademarks are trademarks of Dell Inc. or its subsidiaries. Other trademarks may be trademarks of their respective owners.