

Impact Pin Moisture Probe

P/N: MR05

Copyright

© 2015, FLIR Systems, Inc.

All rights reserved worldwide. Names and marks appearing herein are either registered trademarks or trademarks of FLIR Systems and/or its subsidiaries. All other trademarks, trade names or company names referenced herein are used for identification only and are the property of their respective owners.

Document identity

Publ. No.: MR05

Release:

Commit: 26727

Language:

Modified: 2015-06-12

Formatted: 2015-10-17

Website

<http://www.flir.com>

Customer support

<http://support.flir.com>

Disclaimer

Specifications subject to change without further notice. Camera models and accessories subject to regional market considerations. License procedures may apply. Products described herein may be subject to US Export Regulations. Please refer to exportquestions@flir.com with any questions.



Part number	MR05
Part description	Impact Pin Moisture Probe
	The FLIR MR05 upgrades your FLIR moisture meter to help you easily test for moisture in challenging spots—on rough or uneven surfaces, in corners, in hard woods or high-density materials, and even, with ease, in areas without a dry reference. Made with extra-durable pins and a metallic impact plate that can withstand hammering to drive pins into the hardest materials, the FLIR MR05 lets you tackle the toughest moisture-measurement challenges all day long. Key features include six additional sets of thick and thin pins, an external pin accessory for the FLIR moisture meter mount for extended reach, a 1/4"-20 integrated wrench on the cap to replace pins, a durable BNC connector, a 2 m coiled cord, and a 2 year warranty.
Meter data	
Suitable main unit	MR77 (MR160 and MR176 coming soon)
Cable length	2.45 m (8') uncoiled
Pin length	10 mm (0.4")
Warranty	2 years (with registration)
Meter physical data	
Weight	195 g (0.43 lb)
Dimensions (H x W x L)	8.4 cm x 7.1 cm x 3.8 cm (3.3" x 2.8" x 1.5")
Material	PC-ABS
Color	Black
Shipping information	
Packaging type	Color retail packaging
Packaging contents	MR05, manual, six extra pin sets (three wide, three standard)
Packaging weight	0.4 kg (0.8 lb)
Packaging dimensions (H x W x L)	31.1 cm x 15.2 cm x 5.7 cm (12.25 x 6 x 2.2 in)



Impact Pin Moisture Probe

P/N: MR05

© 2015, FLIR Systems, Inc.

#MR05; r. /26727;

Shipping information	
Inner shipping carton weight	1.8 kg (3.98 lb)
Inner shipping carton dimensions (H x W x L)	58.5 cm x 15.9 cm x 12.7 cm (23" x 7" x 5")
Inner shipping carton quantity	4
Master carton weight	6 kg (13.2 lb)
Master carton dimensions (H x W x L)	60.9 cm x 39.4 cm x 17.8 cm (24" x 16" x 7")
Master carton quantity	12
EAN-13	0793950370056
UPC-12	793950370056
Country of origin	China
Tariff code	9025900000
Technical support	
Website	http://support.flir.com
E-mail	TMSupport@flir.com
Phone	855-499-3662
Repairs	repair@flir.com
Accessories	
Replacement pins (standard) Part No. MR05-PINS1 (1.50–1.55 mm)	
Replacement pins (wide) Part No. MR05-PINS2 (2.26–2.35 mm)	