

#### **FRAME TAPES**

- Unique pistol grip design
- Smooth wind-in mechanism
- Compact design fits into a tool chest
- Steel blade will not stretch

MEASURING



	TYPE / CODE NO.	BLADE SIZE		WEIGHT a	BLADE STYLE	PACKAGING	SHELF PACK OTY.
		WIDTH	LENGTH	WEIGHT G	BLADE STILE	PAGRAGING	SILLI FACK OII.
	FT30CM	13 mm	30 m	648	FT1	Carded	6
	FT50CM	13 mm	50 m	850	FT2	Carded	6
	FT30CME	13 mm / 1/2 in	30 m / 100 ft	648	FT1	Carded	6
	FT50CME	13 mm / 1/2 in	50 m / 150 ft	850	FT2	Carded	6

# **MEASURING WHEELS**

- Measuring wheel, dual foldable, up to 9999,9 mm
- Wheel diameter 160 mm, calibrated to counter
- Wheel brake and counter reset in handle
- Compact, foldable design
- Rubber molded handle Carry bag included
- Centimeters and Meters



- Reset trigger in handle and counter
- Braking trigger in handle
- Patented hinge mechanism handle for storage, folded size 530 mm
- 5 digit counter measures 10.000 m without resetting, 10 cm steps
- Built in kickstand wheel
- Large 305 mm wheel diameter provides more accurate measurements
- particularly on uneven terrain
- Comfortable handling, total length:
- Centimeters and Meters



CODE NO.	DESCRIPTION	PACKAGING	WHEIGHT g	SHELF PACK QTY.
MW16MEU	Measuring Wheel, Ø 160 mm, 6 1/8 in	Boxed	1100	4

#### SHELF DESCRIPTION PACKAGING WHEIGHT CODE NO. Measuring Wheel. MW30MEU 1720 ø 305 mm / 12 in

# **FOLDING RULE SQUARE EDGE**

- Made of Tough, Durable, Engineered Plastic
- Hard Wearing Measure with Easy-to-Read Markings
- Ideal for Tradesmen, DIY and Professional Users
- Yellow Square Edged Rule with Bold Black Markings



CODE NO.	LENGTH	COLOUR	WEIGHT g	BLADE STYLE	PACKAGING	SHELF PACK OTY.
LFSSI	1 m	Yellow	118	LFSSI	Carded	6
LFSME	1 m / 39 in	Yellow	118	LFSME	Carded	6

### **FOLDING RULE BEVELLED EDGE**

- Made of Tough, Durable, Engineered Plastic
- Hard Wearing Measure with Easy-to-Read Markings
- Ideal for Tradesmen, DIY and Professional Users
- White Bevelled Edge Rule with Black and Red Markings



CODE NO.	LENGTH	COLOUR	WEIGHT g	BLADE STYLE	PACKAGING	SHELF PACK OTY.
LFBSI	1 m	White	130	LFBSI	Carded	6

## STAINLESS STEEL RULE

- Rustless Steel, Deeply Etched for Easy Reading
- Upper Edge Subdivided mm and 1/2 mm
- Lower Edge Subdivided 1/8 in, 1/32 in and 1/64 in

CODE NO.	LENGTH	COLOUR	WEIGHT g	BLADE STYLE	PACKAGING	SHELF PACK OTY.
LSR150	150 mm	Stainless Steel With Black Markings	20	SSR	Carded	25
LSR300	300 mm	Stainless Steel With Black Markings	50	SSR	Carded	10
LSR600	600 mm	Stainless Steel With Black Markings	140	SSR	Carded	10
LSR1000	1000 mm	Stainless Steel With Black Markings	450	SSR	Carded	10

44 45