

## 10m Coax High Resolution Monitor VGA Video Cable with Audio HD15 M/M

**Product ID:** MXTHQMM10MA



The MXTHQMM10MA 10-meter High Resolution VGA Cable with Audio is a high quality SVGA cable designed to provide the highest video quality possible through VGA - a single cable solution for connecting both video between a VGA video card and monitor, and audio connections between a sound card and external audio device.

StarTech.com's high resolution VGA cable with audio features high quality male-to-male coaxial VGA cable, and is designed to eliminate picture "ghosting" and fuzzy images that are inherent to non-coaxial cables, while delivering superior EMI interference protection by using ferrite cores near the connector ends.

The 10-meter SVGA cable (VGA Cable with Audio) is backed by StarTech.com's Lifetime Warranty.

### Certifications, Reports and Compatibility



### Applications

- Make video and audio connections using a single cable
- Ideal for high resolution VGA monitors (1920x1200 and above)

### Features

- Triple-coaxial + twisted-pair wire for crystal clear display
- Impedance matched at 75 Ohms for full brightness and vibrant picture color

- Molded connector ends with strain relief
- Ferrite core eliminates EMI interference

---

#### Hardware

Warranty	Lifetime
Number of Conductors	14
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)
Number of Ferrites	2
Regulatory Approvals	UL2919

---

#### Performance

Impedance	75 Ohm
-----------	--------

---

#### Connector(s)

Connector A	1 - 3.5 mm Mini-Jack (3 Position)
	1 - VGA (15 pin, High Density D-Sub)
Connector B	1 - 3.5 mm Mini-Jack (3 Position)
	1 - VGA (15 pin, High Density D-Sub)

---

#### Environmental

Operating Temperature	0 to 60 C
Storage Temperature	-20 to 80 C
Humidity	0 - 80 %RH

---

#### Physical Characteristics

Color	Black
Connector Style	Straight

Wire Gauge	28 AWG
Cable Length	32.8 ft [10 m]
Product Length	32.8 ft [10.0 m]
Product Width	0.0 in [0.0 mm]
Product Height	0.0 in [0.0 mm]
Weight of Product	2.3 lb [1.0 kg]

---

**Packaging Information**

Package Quantity	1
Package Length	13.0 in [33.0 cm]
Package Width	10.0 in [25.5 cm]
Package Height	2.8 in [7.1 cm]
Shipping (Package) Weight	2.4 lb [1.1 kg]

---

**What's in the Box**

Included in Package	1 - 10 m Coax High Resolution Monitor VGA Cable with Audio HD15 M/M
---------------------	---

---

*\*Product appearance and specifications are subject to change without notice.*