

Parrot[®] MINIKIT Neo

Voice controlled
portable Bluetooth
hands-free kit



Control the MINIKIT Neo by voice: make and receive calls without touching any buttons. Say the key word 'MINIKIT' at any time to trigger the voice recognition, and then say the name of the contact you wish to call. When receiving a call, just say 'Accept' or 'Reject'. The kit recognises any voice without need for any programming, matching or training.



All your contacts on your kit
Synchronisation with your phonebook is automatic and all menus are vocal so you can stay focused on driving.

Great sound quality
The NXT flat panel technology provides a clear open sound. Combined with a strong amplifier, it delivers a 3W powerful sound. Digital Signal Processing allows a drastic reduction of noise and a strong echo cancellation.

Connect two phones at once
The MINIKIT Neo features Multipoint, allowing it to connect to two phones simultaneously. Thanks to the Switch function, you can also use both phonebooks to make calls!

Listen to your music
The MINIKIT Neo features Bluetooth Audio Streaming (A2DP). You can listen to all your music on your phone and benefit from the voice commands of your navigation app directly on your kit.

Automatically activated
The kit integrates a vibration sensor to automatically switch on when you get in your car. When you leave the car, the MINIKIT Neo automatically enters Ultra Low Power Mode.

Hours of conversation
The MINIKIT Neo gives up to ten hours of talk-time. Enjoy six months of standby with Ultra Low Power Mode. The MINIKIT Neo will tell you the remaining battery time vocally upon request.

Simple pairing
The MINIKIT Neo will vocally guide you through the entire pairing process. Once your phone is paired, the Bluetooth connection with the kit is always automatic. If you have a NFC-compatible phone, all you have to do is hold it to the MINIKIT Neo to connect.

Easy update
Benefit from new features or change the language of your MINIKIT Neo by downloading new software versions for free. To update, just drag n' drop the software file on the MINIKIT Neo's folder on your computer.

Compact and sleek design
The MINIKIT Neo combines the best of technology in a compact and stylish design. The integrated clipping system is compatible with all sun-visors and can be reversed easily with only one hand when you fold or unfold the sun visor.

Voice controlled portable Bluetooth hands-free kit



for mobile phone
for Smartphone
for iPhone



Parrot MINIKIT Neo

Technical specifications

GENERAL

- Dual Mode (Multipoint): simultaneous connection of two Bluetooth phones
- Number of contacts : 2,000 per phone – Total of 20,000 contacts maximum per MINIKIT Neo
- Language : one language per version
- Pairing capacity : maximum of 10 devices per MINIKIT Neo
- Battery : Lithium Ion – 1000mAh
- Battery life : over 10 hours in conversation, over 15 days in stand-by, over 6 months in deep sleep mode
- Charging time : 3 hours maximum – 5V / 500mA
- Easy Pairing Process and NFC tag
- Automatic connection by pairing order
- Software update via USB port

INTERFACE

- 1 button On / Off / Battery level
- 3 buttons Operation, including one jog wheel
- 3 LEDs (green and red), including one for battery charging

TELEPHONY

- Green button : answer, call a contact from the phonebook, initiate voice recognition, confirm, private mode
- Red button : hang up, cancel, exit menus
- Rotary knob : access the menus, adjust the volume, send DTMF signal

HARDWARE

- SIP6 processor at 416 MHz
- Flash memory : 128MB (1Gb)
- RAM memory : 32MB (256Mb) – DDR

AUDIO

- 3W speaker
- Full duplex
- Built-in multidirectional microphone
- Output via NXT vibrating panel
- HDR < 1%
- Noise reduction : Parrot NR v3.0
- Echo cancellation : Parrot APA v1.5
- Voice prompts for all menus
- Speaker Independent Voice Recognition
- Natural Text-To-Speech (reads the names in the phonebook)

DIMENSIONS & WEIGHT

- Length : 94 mm – 3.70 in
- Width : 54 mm – 2.12 in
- Thickness : 39 mm – 1.53 in
- Weight : 69 g – 2.43 oz

BLUETOOTH

- Bluetooth v3.0
- Profiles : HFP 1.6 (Hands Free Profile), A2DP (Advanced Audio Distribution Profile), PBAP (Phone Book Access Profile)
- Other synchronisation protocols : SyncML – Synchro AT – Synchro Nokia
- Bluetooth range : 10 meters max. – 30 feet max.
- Pairing code : '0 0 0 0' by PIN code – No pairing code with NFC tag

PACKAGE CONTENT

- 1x Parrot MINIKIT Neo
- 1x USB / micro-USB cable
- 1x 12/24V accessory socket charger – USB out
- 1x Quick Start Guide

The Bluetooth wireless technology enables voice and data to be sent via a shortdistance radio link. It connects a wide range of electronic equipment without requiring additional cables. Furthermore, it extends the communication possibilities for mobile phones and a large number of devices.



DUAL MODE



VOICE RECOGNITION

3W

NFC

SIMPLE PAIRING

A2DP

www.parrot.com