



SEAMLESS DATA CONNECTION

MOBILE C21

Type-A

Type-C

Data Access Between All Devices

The Mobile C21 dual USB flash drive is a crowd-pleaser. With USB Type-A and Type-C outputs on opposite ends, it's easy to access, move, or back-up data between next-gen Type-C devices and older Type-A PCs or Macs. Free up space on Type-C devices such as smartphones and tablets and quickly make room for new photos, videos, and songs by offloading that data on to older notebooks. Plus, with USB OTG support, you can directly connect Type-C devices to the Mobile C21 for quick back-ups or to easily access the additional storage space without a computer.

USB 3.2 Gen 1



USB Type-A + USB Type-C

Forward With C, Backwards With A

With up to 128GB of storage capacity at your fingertips, the Mobile C21 is the perfect solution to gain additional storage space and bridge the gap between old and new devices. The USB 3.2 Gen 1 interface grants speedy data transfers, making it a quick and easy transfer solution. Plus, the reversible Type-C connector has a symmetric design that is always right-side-up, making it easy and foolproof to plug in to compatible devices. Take the Mobile C21 with you as one solution for both forward and backwards compatibility.

USB Flash Drive

Mobile C21



Features

- Super-speed data transfer with Type-C & Type-A USB 3.2 Gen 1 interfaces
- Up to 128GB of storage capacity for instant storage expansion
- Supports OTG devices for direct access without needing to connect to a computer
- True Plug & Play Technology eliminates the need for external power
- Protected against splashing water, vibration, and dust via COB technology
- Simpler and quicker alternative to cloud storage as the bridge between phones and computers
- Super compact and portable lidless design fits in your fingertips
- Recuva File Recovery allows for recovery of erased files, such as digital photos, documents, songs, and videos
- Free SP Widget software available for download for backup & restore, AES 256-bit encryption, and cloud storage

Specifications

- Capacity: 16GB, 32GB, 64GB, 128GB
- Dimensions: 26.7mm x 18.6mm x 5.4mm
- Weight: 2.5g
- Color: Orange
- Interface: Type-C / Type-A USB 3.2 Gen 1 (USB 3.1, USB 3.0, USB 2.0 compatible)
- OS Compatibility:
 - Desktop: Windows 11/10/8.1/8/7, Mac OS 10.3.X or later, Linux 2.6.X or later
 - Mobile: Android 4.1.X* or later (*For USB Type-C ready mobile devices)
- Material: Metal + Plastic
- Operating Temperature: 0°C - 70°C
- Certification: BSMI, CE, FCC, EAC
- Warranty: 5 year limited warranty