

PM
PM 2.7/2.6 MC NE WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Weidmüller has established new market standards with its MultiCard product line. This system is being continually extended with over 200 variants and by consistently extending the portfolio.

General ordering data

| | |
|--------------------|--|
| Type | PM 2.7/2.6 MC NE WS |
| Order No. | 1323710000 |
| Version | PM, Pusher markers, 2.7 x 2.6 mm, Pitch in mm (P): 3.50 Weidmueller, White |
| GTIN (EAN) | 4050118126778 |
| Qty. | 960 pc(s). |
| compatible printer | 1925000000 1139400000 1324380000 |

Data sheet

PM PM 2.7/2.6 MC NE WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|--------|-----------------|------------|
| Length | 2.7 mm | Length (inches) | 0.106 inch |
| Width | 2.6 mm | Width (inches) | 0.102 inch |
| Net weight | 0.07 g | | |

General data

| | | | |
|-----------------------------------|---------------------|-----------------------------------|--------------|
| Application/manufacture | Weidmueller | Colour | White |
| Length | 2.7 mm | Material | Polyamide 66 |
| Operating temperature range, max. | 100 °C | Operating temperature range, min. | -40 °C |
| Recommended industries | Device manufacturer | UL 94 flammability rating | V-2 |
| Width | 2.6 mm | | |

Connector markers

| | |
|-----------------|--------|
| Pitch in mm (P) | 3.5 mm |
|-----------------|--------|

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 5.0 | EC001288 | ETIM 6.0 | EC001288 |
| eClass 6.2 | 27-14-91-29 | eClass 7.1 | 27-14-91-29 |
| eClass 8.1 | 27-14-91-03 | eClass 9.0 | 27-14-11-37 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|---------------------------------|---------------------------------------|
| M-Print® PRO configuration file | mc_pm_2-7_2-6_mcf.zip |
|---------------------------------|---------------------------------------|

Data sheet

PM
PM 2.7/2.6 MC NE WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings



Drawing

